

Electrical sub-base VAVE-L1-1R8-LR

Part number: 573920

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark arresting Holding current reduction
Signal status display	LED
Nominal operating voltage DC	24 V
Immunity to surge	0.8 kV
Pollution degree	3
Approval	RCM
CE mark (see declaration of conformity)	To EU EMC Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Product weight	3.2 g
Electrical connection	M8 / - Plug connector/socket
Protective conductor connection	Not provided
Type of mounting	On solenoid valve via self-tapping screw
Housing colour	Black
Note on materials	RoHS compliant
Material cover	Process automation
Material seals	EPDM
Material housing	Process automation
Material screws	Tempered steel