


Pneumatic valve VUWG-L10-T32H-M-M7

Part number: 574257

FESTO



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | 2x3/2-way, open/closed, monostable |
| Type of actuation | Pneumatic |
| Valve size | 10 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 140 l/min |
| pneumatic working port | M7 |
| Operating pressure | -0.9 bar ... 10 bar |
| Design | Piston gate valve |
| Type of reset | Mechanical spring |
| Grid dimension | 10.5 mm |
| Exhaust-air function | Can be throttled |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | None |
| Type of piloting | Direct |
| Flow direction | Reversible |
| Symbol | 00992944 |
| lap | Overlap |
| Pilot pressure | 3 bar ... 10 bar |
| Suitability for vacuum | Yes |
| Switching time off | 7 ms |
| Switching time on | 6 ms |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 5 according to ISO 14644-1 |
| Media temperature | -5 °C ... 50 °C |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C ... 60 °C |
| Product weight | 51 g |
| Type of mounting | On PR rail With through-hole |
| Pilot air port 12 | M5 |
| Pilot air port 14 | M5 |
| Pneumatic connection, port 1 | M7 |

| Feature | Value |
|------------------------------|----------------|
| Pneumatic connection, port 2 | M7 |
| Pneumatic connection, port 3 | M7 |
| Pneumatic connection, port 4 | M7 |
| Pneumatic connection, port 5 | M7 |
| Note on materials | RoHS compliant |
| Material seals | HNBR NBR |
| Material housing | anodised |