

# Solenoid coil VACF-B-C1-1

Part number: 8030811



 General operating condition

## Data sheet

Feature	Value
Type of actuation	Electrical
Mounting position	Any
Conforms to standard	IEC 61010-1
Duty cycle	100%
Insulation material class	H
Characteristic coil data	24 V DC: 3.3 W
Permissible voltage fluctuations	+/-10%
Approval	c UL us - Recognised (Oil)
Certificate issuing authority	UL MH18122
Restrictions for environmental and media temperature	-20 - 50 °C
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-20 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-20 °C ... 60 °C
Product weight	54.1 g
Electrical connection 1, connection type	Plug
Electrical connection 1, connector system	Plug pattern type C to EN 175301-803
Electrical connection 1, number of connections/cores	3
Electrical connection 1, connection pattern	00995860
Electrical connection 1, type of mounting	Central screw M2.5
Type of mounting	Via knurled nut
Note on materials	RoHS compliant
Material housing	Process automation Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper