

Certificate of Compliance

Certificate Number **20090902-MH19482**
Report Reference **MH19482, 2009 September 1**
Issue Date **2009 September 2**

Page 1 of 2



Issued to: **FESTO AG & CO KG**
RUITER STR 82
73734 ESSLINGEN GERMANY

*This is to certify that
representative samples of*



COMPONENT - VALVES, ELECTRICALLY OPERATED
See Addendum for Models

*Have been investigated by Underwriters Laboratories Inc.® in
accordance with the Standard(s) indicated on this Certificate.*

Standard(s) for Safety: UL 429 - Electrically Operated Valves, Fifth Edition
C22.2, No. 139-1982 - Electrically Operated Valves, Second Edition

Additional Information: See Addendum for Ratings

Only those products bearing the UL Recognized Component Marks for the U.S. and Canada should be considered as being covered by UL's Recognition and Follow-Up Service and meeting the appropriate U.S. and Canadian requirements.

The UL Recognized Component Mark for the U.S. generally consists of the manufacturer's identification and catalog number, model number or other product designation as specified under "Marking" for the particular Recognition as published in the appropriate UL Directory. As a supplementary means of identifying products that have been produced under UL's Component Recognition Program, UL's Recognized Component Mark:  may be used in conjunction with the required Recognized Marks. The Recognized Component Mark is required when specified in the UL Directory preceding the recognitions or under "Markings" for the individual recognitions. The UL Recognized Component Mark for Canada consists of the UL Recognized Mark for Canada:  and the manufacturer's identification and catalog number, model number or other product designation as specified under "Marking" for the particular Recognition as published in the appropriate UL Directory.

Look for the UL Recognized Component Mark on the product

Issued by:
Dawid Piech, Associate Project Engineer
Underwriters Laboratories Inc.

Reviewed by:
Henry Wallerbos, Senior Project Engineer
Underwriters Laboratories Inc.

Certificate of Compliance

Certificate Number **20090902-MH19482**
Report Reference **MH19482, 2009 September 1**
Issue Date **2009 September 2**

Page 2 of 2



This is to verify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Models:

Valving Systems, Cat. Nos. series MS6 or MS6N, followed by SV, followed by 1/2, AGB, AGC, AGD, AGE, AQN, AQP, AQR or AQS, followed by D, followed by 10V24, may be followed by A4, AD1, AD2, AD3 or AD4, may be followed by MP1 or MP3, may be followed by WPB, may be followed by Z, followed by a six digit number code, followed by 4 suffixes consisting of any combination of letters and/or numbers, may be followed additionally by any combinations of letters and/or numbers.

RATINGS:

Fluid:	Air or inert gas
Maximum Operating Pressure (Differential):	0.35-1.0 MPa (3.5-10 Bar, 50-145 PSI)
Maximum External Body Pressure:	0.35-1.0 MPa (3.5-10 Bar, 50-145 PSI)
Maximum Fluid Temperature:	-10°C to +50°C
Maximum ambient Temperature:	-10°C to +50°C
Electrical (for each separate pilot valve):	24 Vdc NEC Class 2 only, Max. 1.6 W

Issued by:
Dawid Piech, Associate Project Engineer
Underwriters Laboratories Inc.

Reviewed by:
Henry Wallerbos, Senior Project Engineer
Underwriters Laboratories Inc.