


**FOR IMMEDIATE RELEASE****Media Contact:**

Steve Sterling  
952.935.0078  
steve@sterlingpr.net

**MPA-L Valve Manifold****Highly Scalable Valve Manifold for Value and Performance**

The MPA-L valve manifold offers a perfect mix of value and performance. It is scalable down to a single valve slice, so directional valves can be adapted to any application. This saves costs and reduces size. The sub-base is of a rugged, polymer design, which offers good corrosion resistance, and light weight. The valves are electrically connected to an internal PCB, which also provides exact coil allocation, no wasted logical connections. Many electric multi-pin connector options are available, as well as network interfaces to most common industrial and Ethernet protocols, via Festo's CPX distributed I/O family. All standard valve functions are available, including; 5/2, 5/3, and the cost/space saving dual 3/2 types. All valves use Festo's patented cartridge principle, which is proven to be extremely durable, and offers outstanding flow rates. There are well over 10 million valves with this technology in service to date.

The manifold is suited for most pneumatic applications, for factory and process automation. The high flow rate to size ratio makes it universal for applications from food and packaging to Semiconductor. The valve can run pressure and vacuum, with multiple zones. Contact Festo to see if the MPA-L can reliably solve all of your valve needs.

**Highlights**

- Up to 32 valve locations, max flow rate to 360 NI/min
- Inch and Metric ports for all markets
- Full range of pneumatic functions and accessories such as pressure regulators
- D-sub, IDC / Ribbon cable connectors, bus networks, and Ethernet connections

**Festo Corporation**

395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788  
Tel: 631.435.0800  
Fax: 631.231.9215  
www.festo.com/usa



**News Release**

For more details, please visit: <http://www.festo.com/us/mpa-l>

**Festo** is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. We are best known for our pneumatic products (with a wide selection of inch and metric products), but our dedication to the advancement of automation extends beyond technology to the education of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

**Festo Contact Information for publication:**

Tel: 800.99.FESTO; Fax: 800.96.FESTO

E-mail: [customerservice@us.festo.com](mailto:customerservice@us.festo.com)

Website: [www.festo.com/usa](http://www.festo.com/usa)

**Media Contact:**

Steve Sterling

952.935.0078

[steve@sterlingpr.net](mailto:steve@sterlingpr.net)

**Festo Corporation**

395 Moreland Road

P.O. Box 18023

Hauppauge, NY 11788

Tel: 631.435.0800

Fax: 631.231.9215

[www.festo.com/usa](http://www.festo.com/usa)