


Axial kit EAMM-A-D19-42A

Part number: 1087642

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	50 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	0.28 kgmm ²
Transmittable torque	1.1 Nm
Product weight	130 g
Interface code, actuator	D19
Interface code, motor in	42A
Note on materials	RoHS-compliant