

One-way flow control valve GRLZ-1/4-RS-B

Part number: 151198

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | Supply air one-way flow control function |
| Pneumatic connection, port 1 | Female thread G1/4 |
| Pneumatic connection, port 2 | Male thread G1/4 |
| Adjustment component | Knurled screw |
| Type of mounting | Screw-in |
| Standard nominal flow rate in flow control direction | 610 l/min |
| Standard nominal flow rate in blocked direction | 450 l/min ... 820 l/min |
| Ambient temperature | -10 °C ... 60 °C |
| Explosion protection | The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Mounting position | Any |
| Symbol | 00991453 |
| Operating pressure complete temperature range | 0.3 bar ... 10 bar |
| Standard flow rate in flow control direction 0.6->0 MPa (6->0 bar, 87->0 psi) | 1200 l/min |
| Standard flow rate in non-return direction 0.6->0 MPa (6->0 bar, 87->0 psi) | 885 l/min ... 1615 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 4 according to ISO 14644-1 |
| Media temperature | -10 °C ... 60 °C |
| Nominal size | 6 mm |
| Max. tightening torque | 11 Nm |
| Product weight | 59 g |
| Material screwed plug | Wrought aluminium alloy |
| Note on materials | RoHS compliant |

| Feature | Value |
|--------------------------|---------------|
| Material seals | NBR |
| Material adjusting screw | Brass |
| Material swivel fitting | Die-cast zinc |