

Compact cylinder AEVUZ-32-25-P-A

Part number: 157230

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Stroke | 25 mm |
| Piston diameter | 32 mm |
| Piston rod thread | M6 |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | Any |
| Mode of operation | Single-acting Pulling |
| Piston-rod end | Female thread |
| Design | Piston Piston rod |
| Position detection | Via proximity switch |
| Symbol | 00991204 |
| Variants | Piston rod at one end |
| Operating pressure | 0.08 MPa ... 1 MPa |
| Operating pressure | 0.8 bar ... 10 bar |
| Operating pressure | 11.6 psi ... 145 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in end positions | 0.4 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 382 N |
| Moving mass for 0 mm stroke | 49 g |
| Additional moving mass per 10 mm stroke | 9 g |
| Basic weight for 0 mm stroke | 300 g |
| Additional weight per 10 mm stroke | 40 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection | G1/8 |
| Material collar screws | Galvanised steel |
| Material cover | Wrought aluminium alloy |
| Material dynamic seals | NBR TPE-U(PU) |
| Material piston rod | High-alloy stainless steel |
| Material cylinder barrel | Wrought aluminium alloy |