

Ball valve VZBE-1-T-63-F-3L-F05-V15V15

Part number: 4834292

FESTO



 General operating condition

Data sheet

Feature	Value
Design	L-bore
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Inline installation
Connection Process valve	1 NPT
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F05
Inside diameter	20 mm
Nominal size DN	25
Valve function	3/2
Flow direction	Reversible
Nominal pressure PN	63
Breakaway torque at differential pressure, nominal pressure, process valve PN	25.2 Nm
Based on standard	ISO 5211
Symbol	00991888
Medium	Vapour Compressed air to ISO 8573-1:2010 [-:~:] Inert gases Water Neutral fluids
Media temperature	-20 °C ... 200 °C
Flow rate Kv L hole	16 m ³ /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Cast stainless steel
Material number housing	1,4408
Material seat seal	PTFE
Material seals	PTFE

Feature	Value
Material ball	Cast stainless steel
Material number ball	1,4408
Material shaft	High-alloy stainless steel
Material number shaft	1,4401
Product weight	1618 g
Approval	CRN
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	4 - Very high corrosion stress