

# Compact cylinder DPDM-20-5-S-PA

Part number: 4840807

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	20 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Mode of operation	Pushing Single-acting
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Symbol	00991729
Variants	Piston rod at one end
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi)	160 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	160 N
Moving mass for 0 mm stroke	34.5 g
Additional moving mass per 10 mm stroke	4 g
Basic weight for 0 mm stroke	117 g
Additional weight per 10 mm stroke	22 g
Type of mounting	With through-hole With female thread
Pneumatic connection	M5
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel