


# Axial kit EAMM-A-D50-100A-S1

Part number: 2734288

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	84 mm
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP65
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	34.8 kgmm <sup>2</sup>
Transmittable torque	21 Nm
Product weight	1180 g
Interface code, actuator	D50
Interface code, motor in	100A
Note on materials	RoHS-compliant