

Compact cylinder DPDM-Q-32-5-P-PA

Part number: 4828499

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	32 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Mode of operation	Single-acting Pulling
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Symbol	00991733
Variants	Piston rod at one end
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	377 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	377 N
Moving mass for 0 mm stroke	109 g
Additional moving mass per 10 mm stroke	10.5 g
Basic weight for 0 mm stroke	334 g
Additional weight per 10 mm stroke	52.5 g
Type of mounting	With through-hole With female thread
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel