

# Electric cylinder ESBF-BS-100-400-5P

Part number: 574117

FESTO



 General operating condition

## Data sheet

Feature	Value
Working stroke	400 mm
Size	100
Stroke	400 mm
Piston rod thread	M20x1.5
Reversing backlash theoretical	30 µm
Spindle diameter	40 mm
Spindle pitch	5 mm/U
Torsional backlash at piston rod +/-	0.5 deg
Based on standard	ISO 15552
Mounting position	Any
Piston-rod end	Male thread
Type of motor	Servo motor
Position detection	Via proximity switch
Design	Electric cylinder with ball screw
Spindle type	Ball screw
Symbol	00991941
Protection against torque/guide	With plain-bearing guide
Max. acceleration	5 m/s <sup>2</sup>
Max. rotational speed	2010 rpm
Max. speed	0.17 m/s
Repetition accuracy	±0.01 mm
Duty cycle	100%
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 60 °C
Suitable for use with food	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C ... 60 °C
Max. drive torque	16.9 Nm
Max. radial force at drive shaft	1100 N
Max. feed force Fx	17000 N
Frictional torque independent of load	0.7 Nm
Reference value effective load, horizontal	1700 kg
Reference value effective load, vertical	1700 kg
Mass moment of inertia JH per metre of stroke	18.978 kgcm <sup>2</sup>

<b>Feature</b>	<b>Value</b>
Mass moment of inertia JL per kg of working load	0.00633 kgcm <sup>2</sup>
Mass moment of inertia JO	4.6963 kgcm <sup>2</sup>
Maintenance interval	Lifetime lubrication
Moving mass for 0 mm stroke	8786 g
Additional moving mass per 10 mm stroke	132 g
Basic weight for 0 mm stroke	11123 g
Additional weight per 10 mm stroke	193 g
Type of mounting	With female thread Or accessories
Interface code, actuator	D100
Note on materials	RoHS compliant
Material cover	Cast aluminium, coated
Material piston rod	High-alloy stainless steel
Material screws	Galvanised steel
Material ball screw nut	Bearing steel
Material spindle	Bearing steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy