


# End plate VABE-S1-2RZ-G34

Part number: 8032672

FESTO



 [General operating condition](#)

## Data sheet

| Feature                            | Value  |
|------------------------------------|--|
| Construction width                 | 44 mm  |
| Exhaust-air function               | With flow control option   |
| Based on standard                  | ISO 5599-1   |
| Operating pressure                 | -0.09 MPa ... 1.6 MPa  |
| Operating pressure                 | -0.9 bar ... 16 bar  |
| Suitability for vacuum             | yes  |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 0 - No corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Storage temperature                | -20 °C ... 60 °C   |
| Media temperature                  | -10 °C ... 50 °C   |
| Pilot medium                       | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Ambient temperature                | -10 °C ... 50 °C   |
| Product weight                     | 370 g  |
| Type of mounting                   | Via through-hole for M6 screw  |
| Pilot air port 12/14               | G1/4   |
| Pneumatic connection, port 1       | G3/4   |
| Pneumatic connection, port 3       | G3/4   |
| Pneumatic connection, port 5       | G3/4   |
| Note on materials                  | RoHS-compliant   |
| Material end plate                 | Die-cast aluminium   |