



Pressure transmitter SPTE-V1R-S6-B-2.5K

Part number: 571470

FESTO



 General operating condition

Data sheet

Feature	Value
Symbol	00992257
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Certificate issuing authority	UL E322346
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Measurement method	Piezoresistive pressure sensor
Start value for pressure measuring range	0 MPa
Start value for pressure measuring range	0 bar
Start value for pressure measuring range	0 psi
End value for pressure measuring range	-0.1 MPa
End value for pressure measuring range	-1 bar
End value for pressure measuring range	-14.5 psi
Overload pressure	0.5 MPa
Overload pressure	5 bar
Overload pressure	72.5 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Media temperature	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Accuracy in ± % FS	3 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature coefficient in ± %FS/K	0.05 %FS/K
Analogue output	1 - 5 V
Rise time	1 ms
Min. load resistance voltage output	15 kOhm
Short circuit current rating	For all electrical connections
Operational voltage range DC	10 V ... 30 V
Reverse polarity protection	For all electrical connections
Electrical connection	Cable Open end
Cable length	2.5 m
Type of mounting	Plug-in

Feature	Value
Mounting position	optional
Pneumatic connection	Push-in sleeve QS-6
Product weight	35 g
Material housing	PA-reinforced
Material sealing ring	FPM
Degree of protection	IP40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1