

# Ball valve VZBE-3/8-T-63-F-3L-F04-M-V15V15

Part number: 8096944

FESTO



 General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Design  | L-hole   |
| Type of actuation   | Mechanical   |
| Sealing principle   | Soft   |
| Mounting position   | optional   |
| Type of mounting  | In-line installation   |
| Connection Process valve  | 3/8 NPT  |
| Switching position indicator  | Slot direction = flow direction  |
| Flange hole pattern   | F04  |
| Inside diameter   | 11 mm  |
| Nominal size DN   | 10   |
| Valve function  | 3/2  |
| Flow direction  | Reversible   |
| Nominal pressure PN   | 63   |
| Breakaway torque at differential pressure, nominal pressure, process valve PN | 9.6 Nm   |
| Based on standard   | ISO 5211   |
| Symbol  | 00991888   |
| Medium  | Vapour<br>Compressed air to ISO 8573-1:2010 [-:~:]<br>Inert gases<br>Water<br>Neutral fluids |
| Media temperature   | -20 °C ... 200 °C  |
| Flow rate Kv L hole   | 1.2 m <sup>3</sup> /h  |
| Note on materials   | RoHS-compliant   |
| LABS (PWIS) conformity  | VDMA24364 zone III   |
| Material housing  | Stainless steel casting  |
| Material number housing   | 1.4408   |
| Material seat seal  | PTFE   |
| Material seals  | PTFE   |

| <b>Feature</b>                 | <b>Value</b>   |
|--------------------------------|--|
| Material ball                  | Stainless steel casting  |
| Material number ball           | 1.4408   |
| Material shaft                 | High-alloy stainless steel   |
| Material number shaft          | 1.4401   |
| Product weight                 | 700 g  |
| Approval                       | CRN  |
| Explosion protection           | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Corrosion resistance class CRC | 4 - Very high corrosion stress                                     |