

Trunnion support CRLNZG-100/125

Part number: 161877

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	100/125
Based on standard	ISO 15552
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	739 g
Note on materials	RoHS-compliant
Material mounting	High-alloy stainless steel
Material bearing	Polymer