

# One-way flow control valve GRLA-1/8-QS-4-D

Part number: 193143

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | Exhaust air one-way flow control function  |
| Pneumatic connection, port 1  | QS-4   |
| Pneumatic connection, port 2  | G1/8   |
| Adjustment component  | Slotted head screw   |
| Type of mounting  | Screw-in   |
| Standard nominal flow rate in flow control direction                          | 160 l/min  |
| Standard nominal flow rate in blocked direction                               | 120 l/min ... 190 l/min  |
| Ambient temperature   | -10 °C ... 60 °C   |
| Maritime classification   | See certificate  |
| Mounting position   | optional   |
| Symbol  | 00991452   |
| Operating pressure complete temperature range                                 | 0.2 bar ... 10 bar   |
| Standard flow rate in flow control direction 0.6-10 MPa (6-10 bar, 87-10 psi) | 250 l/min  |
| Standard flow rate in non-return direction 0.6-10 MPa (6-10 bar, 87-10 psi)   | 270 l/min ... 300 l/min  |
| Operating medium  | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium  | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity  | VDMA24364-B1/B2-L  |
| Cleanroom suitability, measured according to ISO 14644-14                     | Class 4 according to ISO 14644-1   |
| Media temperature   | -10 °C ... 60 °C   |
| Nominal torque  | 3 Nm   |
| Tolerance for nominal tightening torque                                       | ± 10%  |
| Product weight  | 22 g   |
| Material screwed plug   | Wrought aluminium alloy  |
| Note on materials   | RoHS-compliant   |
| Material seals  | NBR  |
| Material release ring   | POM  |
| Material adjusting screw  | Brass  |

| Feature                 | Value                      |
|-------------------------|----------------------------|
| Material swivel fitting | Die-cast zinc<br>Chromated |