

Guided drive DFM-20-50-P-A-GF

Part number: 170844

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	50 mm
Piston diameter	20 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Symbol	00991737
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	0.2 J
Max. force Fy	709.3 N
Max. force Fy static	709.3 N
Max. force Fz	709.3 N
Max. force Fz static	709.3 N
Max. moment Mx	20.57 Nm
Max. torque Mx static	20.57 Nm
Max. moment My	16.31 Nm
Max. torque My static	16.31 Nm
Max. moment Mz	16.31 Nm
Max. torque Mz static	16.31 Nm
Max. permissible torque load Mx as a function of stroke	3.85 Nm
Max. effective load dependent upon stroke at defined distance xs	103 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	141 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	188 N

Feature	Value
Moving mass	582 g
Product weight	1158 g
alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel