


# Guided drive DFM-20-30-P-A-KF

Part number: 170917

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	30 mm
Piston diameter	20 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Position detection	Via proximity switch
Symbol	00991737
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-5 °C ... 60 °C
Impact energy in end positions	0.2 J
Max. force Fy	408 N
Max. force Fy static	510 N
Max. force Fz	408 N
Max. force Fz static	510 N
Max. moment Mx	11.84 Nm
Max. torque Mx static	14.79 Nm
Max. moment My	4.49 Nm
Max. torque My static	5.61 Nm
Max. moment Mz	4.49 Nm
Max. torque Mz static	5.61 Nm
Max. permissible torque load Mx as a function of stroke	2.08 Nm
Max. effective load dependent upon stroke at defined distance xs	42 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	141 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	188 N

<b>Feature</b>	<b>Value</b>
Moving mass	400 g
Product weight	822 g
Centre of gravity of moving mass as a function of stroke	20.8 mm
alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel