

Short-stroke cylinder AEVC-25-10-A-P

Part number: 188170

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	25 mm
Spring return force with retracted piston rod	15 N
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing Single-acting
Design	Piston Piston rod
Position detection	Without
Symbol	00991730
Operating pressure	0.15 MPa ... 1 MPa
Operating pressure	1.5 bar ... 10 bar
Operating pressure	21.75 psi ... 145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	272 N
Moving mass	25 g
Product weight	110 g
Type of mounting	Either: With through-hole With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy Anodised
Material seals	NBR TPE-U(PIU)
Material housing	Wrought aluminium alloy Anodised
Material piston rod	High-alloy steel