

Connecting cable

NEBU-M12G5-E-7.5-Q8N-M12G5

Part number: 574322

FESTO



 General operating condition

Data sheet

Feature	Value
Conforms to standard	EN 61076-2-101
Cable designation	Without inscription label holder
Frequency of connection	100
Product weight	635 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, used connections/cores	5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00995384
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plugs
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 2, number of connections/cores	5
Electrical connection 2, used connections/cores	5
electrical connection 2, type of mounting	Screw-type lock
Electrical connection 2, connection pattern	00995383
Operational voltage range DC	0 V ... 60 V
Operational voltage range AC	0 V ... 60 V
Current rating at 40° C	4 A
Immunity to surge	1.5 kV
Cable length	7.5 m
Cable characteristic	Suitable for energy chains
Test conditions cable	Bending strength: to Festo standard Test conditions on request Energy chain: > 5 million cycles, bending radius 75 mm
Bending radius, fixed cable	21 mm
Bending radius, moving cable	71 mm
Cable diameter	7 mm
Cable diameter tolerance	± 0.1 mm
Cable structure	5 x 1 mm ²

Feature	Value
Nominal cross section conductor	1 mm ²
Degree of protection	IP65 IP68 IP69K
Note on degree of protection	In assembled state
Special characteristics	Oil resistant
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with moving cable	-5 °C ... 80 °C
Storage temperature	-25 °C ... 80 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Free of halogen Free of phosphoric acid ester
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Material housing	TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulating sheath	PP