


Solenoid valve

VUVS-LK20-M32C-AD-G18-1C1+GL-S

FESTO

Part number: 8060299



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | 3/2-way, closed, monostable |
| Type of actuation | Electric |
| Valve size | 21 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 550 l/min |
| pneumatic working port | G1/8 |
| Operating voltage | 24V DC |
| Operating pressure | 0.15 MPa ... 0.8 MPa |
| Operating pressure | 1.5 bar ... 8 bar |
| Design | Piston gate valve |
| Type of reset | Pneumatic spring |
| Degree of protection | IP65 With plug socket To IEC 60529 |
| Nominal size | 5.2 mm |
| Exhaust-air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | optional |
| Manual override | Detenting Non-detenting |
| Type of piloting | Pilot actuated |
| Pilot air supply | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991183 |
| lap | Overlap |
| b value | 0.38 |
| C value | 2.66 l/sbar |
| Switching time off | 20 ms |
| Switching time on | 16 ms |
| Duty cycle | 100% |
| Max. positive test pulse with 0 signal | 2700 µs |
| Max. negative test pulse with 1 signal | 1100 µs |
| Characteristic coil data | 24 V DC: 2.4 W |
| Permissible voltage fluctuations | +/- 10 % |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |

| Feature | Value |
|---------------------------------|--|
| Vibration resistance | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Media temperature | -5 °C ... 50 °C |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 133 g |
| Electrical connection | 3-pin Socket Screw terminal |
| Cable diameter | 4 mm ... 6 mm |
| Nominal cross section conductor | 0.34 mm ² ... 0.5 mm ² |
| Type of mounting | Either: On manifold rail With through-hole |
| Breather connection | Not ducted |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Pneumatic connection, port 3 | G1/8 |
| Note on materials | RoHS-compliant |
| Material seals | HNBR NBR |
| Material housing | Wrought aluminium alloy |
| Material piston slide | Wrought aluminium alloy |