

Revision:
31.07.2026**Divinol DHG ISO 46**
Article No.: 84350

Page 1 of 7

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

84350 Divinol DHG ISO 46

1.2. Relevant identified uses of the substance or mixture and uses advised against**Use of the substance/mixture**

Lubricant

1.3. Details of the supplier of the safety data sheet

Company name: Zeller+Gmelin GmbH & Co. KG
Street: Schlossstr. 20
Place: D-73054 Esslingen
Telephone: +49 (0) 7161 / 802-0
E-mail: info@zeller-gmelin.de
Contact person: Thorsten Grönig
E-mail: produktsicherheit@zeller-gmelin.de
Internet: www.zeller-gmelin.de
Responsible Department: Produktsicherheit / Product Safety

Telefax: +49 (0) 7161 / 802-290

Telephone: +49 (0) 7161 / 802-268

**1.4. Emergency telephone number:**

GBK/Infotrac ID 103334 international: (001) 352 323 3500

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Regulation (EC) No 1272/2008**

This mixture is not classified as hazardous in accordance with Regulation (EC) No 1272/2008.

2.2. Label elements**2.3. Other hazards**

No further relevant information available.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****Chemical characterization**

Mineral oil-based mixture. Mineral oil with DMSO extract < 3 % as measured by IP 346.

Relevant ingredients

none (according to Regulation (EC) No 1907/2006 (REACH))

SECTION 4: First aid measures**4.1. Description of first aid measures****General information**

When in doubt or if symptoms are observed, get medical advice. If unconscious but breathing normally, place in recovery position and seek medical advice. Remove contaminated, saturated clothing immediately.

After inhalation

Remove casualty to fresh air and keep warm and at rest.

After contact with skin

After contact with skin, wash immediately with plenty of water and soap.

After contact with eyes

After contact with the eyes, rinse with water with the eyelids open for a sufficient length of time, then consult an ophthalmologist immediately.

After ingestion

If swallowed, rinse mouth with water (only if the person is conscious). Let water be drunk in little sips (dilution effect). Call a physician immediately. Do NOT induce vomiting.

Revision:
31.07.2026**Divinol DHG ISO 46**
Article No.: 84350

Page 2 of 7

4.2. Most important symptoms and effects, both acute and delayed

When in doubt or if symptoms are observed, get medical advice.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

alcohol resistant foam, Extinguishing powder, Carbon dioxide (CO₂).

Unsuitable extinguishing media

Full water jet.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products: Carbon monoxide Carbon dioxide (CO₂). Do not inhale explosion and combustion gases.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water. Do not allow to enter into soil/subsoil.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures****General advice**

Protective measures: see section 7 + 8.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil. Clean contaminated articles and floor according to the environmental legislation.

6.3. Methods and material for containment and cleaning up**Other information**

Absorb with liquid-binding material (sand, diatomaceous earth, acid- or universal binding agents). Treat the recovered material as prescribed in the section on waste disposal.

6.4. Reference to other sections

Protective measures: see section 7 + 8.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

Use personal protection equipment. Do not eat, drink or smoke when using this product. Provide fresh air. Handle and open container with care. Conditions to avoid: generation/formation of aerosols.

Advice on protection against fire and explosion

No special measures are necessary.

Advice on general occupational hygiene

When using do not eat, drink, smoke, sniff.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Protect against: Frost. Keep away from heat. Protect from direct sunlight. Keep container tightly closed in a cool, well-ventilated place.

7.3. Specific end use(s)

Observe technical data sheet.

SECTION 8: Exposure controls/personal protection

Revision:
31.07.2026

Divinol DHG ISO 46
Article No.: 84350

Page 3 of 7

8.1. Control parameters

Occupational exposure limits

CAS No	Substance	ppm	mg/m ³	fib/cm ³	Category	Origin
-	Mineral Oil pure, highly & severely refined (Inhalable)	-	5		TWA (8 h)	

DNEL/DMEL values

CAS No	Substance	Exposure route	Effect	Value
64742-54-7	distillates (petroleum), hydrotreated heavy paraffinic			
Consumer DNEL, long-term		inhalation	local	1,2 mg/m ³
Consumer DNEL, long-term		oral	systemic	0,74 mg/kg bw/day
Worker DNEL, long-term		inhalation	local	5,58 mg/m ³
Worker DNEL, long-term		dermal	systemic	0,97 mg/kg bw/day
Worker DNEL, long-term		inhalation	systemic	2,73 mg/m ³

PNEC values

CAS No	Substance	Value
64742-54-7	distillates (petroleum), hydrotreated heavy paraffinic	

Additional advice on limit values

- a no restriction
- b End of exposure or end of shift
- c at long-term exposure:
- d before next shift

Y: A risk of reproductive effects needs not to be feared if the occupational exposure limit value (AGW) and the biological limit value (BGW) is kept

Z: A risk of reproductive effects cannot to be excluded if the occupational exposure limit value (AGW) and the biological limit value (BGW) is kept

blood (B)

Urine (U)

8.2. Exposure controls

Appropriate engineering controls

See section 7. No additional measures necessary.

Individual protection measures, such as personal protective equipment

Eye/face protection

Eye glasses with side protection (EN ISO 16321).

Hand protection

Wear suitable gloves. Recommended glove articles: EN ISO 374. Suitable material: NBR (Nitrile rubber). Breakthrough time: > 480 min (Thickness of the glove material: 0.4 mm). Breakthrough times and swelling properties of the material must be taken into consideration. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. Barrier creams can help protecting exposed skin areas. In no case should they be used after contact.

Skin protection

Protective clothing.

Respiratory protection

With correct and proper use, and under normal conditions, breathing protection is not required. When splashes or fine mist form, a permitted breathing apparatus suitable for these purposes must be used. Suitable respiratory protection apparatus: Filtering Half-face mask (EN 149), e.g. FFA P / FFP3.

Revision:
31.07.2026**Divinol DHG ISO 46**
Article No.: 84350

Page 4 of 7

Environmental exposure controls

Do not allow to enter into surface water or drains.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state:	Liquid
Colour:	yellow
Odour:	characteristic

	Test method
Melting point/freezing point:	not determined
Boiling point or initial boiling point and boiling range:	not determined
Flammability:	Non-flammable.
Lower explosion limits:	0,6 vol. %
Upper explosion limits:	6,5 vol. %
Flash point:	> 210 °C EN ISO 2592
Auto-ignition temperature:	not determined
Decomposition temperature:	not determined
pH-Value:	not applicable
Viscosity / kinematic: (at 40 °C)	46 mm ² /s ASTM D 7042
Water solubility:	insoluble
Partition coefficient n-octanol/water:	not determined
Vapour pressure: (at 20 °C)	< 0,1 hPa
Density (at 15 °C):	0,86 g/cm ³ DIN EN ISO 12185
Relative vapour density:	not determined
Particle characteristics:	not applicable

9.2. Other information**Other safety characteristics**

Pour point:	< -24 °C ASTM D 7346
Viscosity / dynamic:	not determined
Flow time:	not determined

Further Information

No further relevant information available.

SECTION 10: Stability and reactivity**10.1. Reactivity**

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions.

10.4. Conditions to avoid

Heat.

10.5. Incompatible materials

No information available.

10.6. Hazardous decomposition products

No information available.

SECTION 11: Toxicological information**11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008**

Revision:
31.07.2026**Divinol DHG ISO 46**
Article No.: 84350

Page 5 of 7

Acute toxicity

Based on available data, the classification criteria are not met.

ATEmix calculated

ATE (oral) > 2000 mg/kg; ATE (dermal) > 2000 mg/kg; ATE (inhalation vapour) > 20 mg/l; ATE (inhalation dust/mist) > 5 mg/l

Irritation and corrosivity

Skin corrosion/irritation: Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation: Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Germ cell mutagenicity: Based on available data, the classification criteria are not met.

Carcinogenicity: Based on available data, the classification criteria are not met.

Reproductive toxicity: Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

11.2. Information on other hazards**Endocrine disrupting properties**

Based on available data, the classification criteria are not met.

Other information

Keeping to the general worker's protection rules and the industrial hygienics, there is no risk in handling this product through the personnel.

SECTION 12: Ecological information**12.1. Toxicity**

Based on available data, the classification criteria are not met.

There are no data available on the mixture itself.

12.2. Persistence and degradability

There are no data available on the mixture itself.

12.3. Bioaccumulative potential

There are no data available on the mixture itself.

12.4. Mobility in soil

No data available

12.5. Results of PBT and vPvB assessment

Based on available data, the classification criteria are not met.

12.6. Endocrine disrupting properties

Based on available data, the classification criteria are not met.

12.7. Other adverse effects

No data available

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Disposal recommendations**

Do not allow to enter into surface water or drains. This material and its container must be disposed of in a safe way. Waste disposal according to directive 2008/98/EC, covering waste and dangerous waste.

List of Wastes Code - residues/unused products

130110 OIL WASTES AND WASTES OF LIQUID FUELS (EXCEPT EDIBLE OILS, AND THOSE IN CHAPTERS 05, 12 AND 19); waste hydraulic oils; mineral based non-chlorinated hydraulic oils; hazardous waste

Revision:
31.07.2026**Divinol DHG ISO 46**
Article No.: 84350

Page 6 of 7

Contaminated packaging

Non-contaminated packages may be recycled. Consult the appropriate local waste disposal expert about waste disposal.

SECTION 14: Transport information**Land transport (ADR/RID)**

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

Air transport (ICAO-TI/IATA-DGR)

<u>14.1. UN number or ID number:</u>	No dangerous good in sense of this transport regulation.
<u>14.2. UN proper shipping name:</u>	No dangerous good in sense of this transport regulation.
<u>14.3. Transport hazard class(es):</u>	No dangerous good in sense of this transport regulation.
<u>14.4. Packing group:</u>	No dangerous good in sense of this transport regulation.

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS:	No
Marine pollutant:	NO

14.6. Special precautions for user

No data available

14.7. Maritime transport in bulk according to IMO instruments

No data available

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 75

Directive 2010/75/EU on industrial emissions:	0 %
---	-----

Information according to Directive 2012/18/EU (SEVESO III):	Not subject to 2012/18/EU (SEVESO III)
---	--

National regulatory information

Water hazard class (D):	1 - slightly hazardous to water
-------------------------	---------------------------------

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information**Changes**

This data sheet contains changes from the previous version in section(s): 1,2,4,5,6,7,8,9,10,11,12,13,14,15,16.

Revision:
31.07.2026**Divinol DHG ISO 46****Article No.: 84350**

Page 7 of 7

Abbreviations and acronyms

ADR: Accord relatif au transport international des marchandises dangereuses par route (Agreement concerning the International Carriage of Dangerous Goods by Road)
RID: Règlement concernant le transport international ferroviaire des marchandises dangereuses (Regulations concerning the International Carriage of Dangerous Goods by Rail)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
ICAO: International Civil Aviation Organization
CAS: Chemical Abstracts Service (a division of the American Chemical Society)
DNEL/DMEL: Derived No-Effect Level / Derived Minimal Effect Level
PNEC: Predicted No Effect Concentration
WEL (UK): Workplace Exposure Limits
TWA (EC): Time-Weighted Average
STEL (EC): Short Term Exposure Limit
ATE: Acute Toxicity Estimate
LD50: Lethal Dose, 50% (median lethal dose)
LC50: Lethal Concentration, 50% (median lethal concentration)
EC50: half maximal Effective Concentration
ErC50: EC50 in terms of reduction of growth rate
AwSV: Verordnung über Anlagen zum Umgang mit wassergefährdenden Stoffen
SPM: synthetic polymer microparticles

Further Information

Safety Data Sheet according to COMMISSION REGULATION (EU) 2020/878 of 18 June 2020 amending Annex II to Regulation (EC) No 1907/2006

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the relevant ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)