

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB

KLÜBER
LUBRICATION

UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : UNISILKON L 641

Article-No. : 022121

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Substance/Mixture : Grease

Recommended restrictions on use : Restricted to professional users.

1.3 Details of the supplier of the safety data sheet

Company : Klüber Lubrication München GmbH & Co. KG
Geisenhausenerstr. 7
81379 München
Deutschland
Tel.: +49 (0) 89 7876 0
Fax: +49 (0) 89 7876 333
info@klueber.com

E-mail address of person responsible for the SDS : mcm@klueber.com

National contact : Klüber Lubrication Great Britain Limited
Unit 10 Pennine Business Park
Longbow Close
Huddersfield
West Yorkshire HD2 1GQ
Great Britain
Tel: +44-1422-205115
Fax: +44-1422-206073
sales@uk.klueber.com

**UNISILKON L 641 =
LUB-KU6**
Festo SE&Co. KG
Ruiter Strasse 82
D-73734 Esslingen
www.Festo.com/en/msds

1.4 Emergency telephone number

Emergency telephone number : +49 89 7876 700 (24 hrs)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008) as amended by GB-CLP Regulation, UK SI 2019/720, and UK SI 2020/1567)

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008) as amended by GB-CLP Regulation, UK SI 2019/720, and UK SI 2020/1567)

Not a hazardous substance or mixture.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Chemical nature : methyl silicone oil
PTFE

Components

Remarks : No hazardous ingredients

SECTION 4: First aid measures

4.1 Description of first aid measures

If inhaled : Remove person to fresh air. If signs/symptoms continue, get medical attention.
Keep patient warm and at rest.
If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact : Remove contaminated clothing. If irritation develops, get medical attention.
Wash off with soap and water.

In case of eye contact : Rinse immediately with plenty of water, also under the eyelids, for at least 10 minutes.
If eye irritation persists, consult a specialist.

If swallowed : Move the victim to fresh air.
Do not induce vomiting without medical advice.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by
UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : No symptoms known or expected.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

Unsuitable extinguishing media : High volume water jet

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products : Carbon oxides
Halogenated compounds
Metal oxides

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus. Use personal protective equipment. Exposure to decomposition products may be a hazard to health.

Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Evacuate personnel to safe areas.
Do not breathe vapours, aerosols.
Refer to protective measures listed in sections 7 and 8.

6.2 Environmental precautions

Environmental precautions : Try to prevent the material from entering drains or water courses.
Local authorities should be advised if significant spillages cannot be contained.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Pick up and transfer to properly labelled containers.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Wash hands and face before breaks and immediately after handling the product.

Hygiene measures : Wash face, hands and any exposed skin thoroughly after handling.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Store in original container. Keep container closed when not in use. Keep in a dry, cool and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Store in accordance with the particular national regulations. Keep in properly labelled containers.

7.3 Specific end use(s)

Specific use(s) : Specific instructions for handling, not required.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Engineering measures

none

Personal protective equipment

Eye/face protection : Safety glasses

Hand protection

Material : Nitrile rubber
Break through time : > 10 min
Protective index : Class 1

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by
UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

Remarks : For prolonged or repeated contact use protective gloves. The break through time depends amongst other things on the material, the thickness and the type of glove and therefore has to be measured for each case.

Skin and body protection : Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.

Respiratory protection : Not required; except in case of aerosol formation.

Filter type : Filter type P

Protective measures : The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Environmental exposure controls

Air : No special environmental precautions required.

Soil :
The product should not be allowed to enter drains, water courses or the soil.

Water :
The product should not be allowed to enter drains, water courses or the soil.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : paste

Colour : white

Odour : characteristic

Odour Threshold : No data available

pH : Not applicable

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by
UK REACH Regulations SI 2019/758 - GB

KLÜBER
LUBRICATION

UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

Melting point/ range : No data available

Boiling point/boiling range : No data available

Flash point : Not applicable

Evaporation rate : No data available

Flammability (solid, gas) : Combustible Solids

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : < 0.001 hPa (20 °C)

Relative vapour density : No data available

Relative density : 1.18 (20 °C)
Reference substance: Water
The value is calculated

Density : 1.18 g/cm³
(20 °C)

Bulk density : No data available

Solubility(ies)

Water solubility : insoluble

Solubility in other solvents : No data available

Partition coefficient: n-octanol/water : No data available

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity

Viscosity, dynamic : No data available

Viscosity, kinematic : Not applicable

Explosive properties : Not explosive

Oxidizing properties : No data available

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by
UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

9.2 Other information

Sublimation point : No data available

Particle Size Distribution : Not applicable

Self-ignition : No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No hazards to be specially mentioned.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions : No dangerous reaction known under conditions of normal use.

10.4 Conditions to avoid

Conditions to avoid : No conditions to be specially mentioned.

10.5 Incompatible materials

Materials to avoid : No materials to be especially mentioned.

10.6 Hazardous decomposition products

Hazardous decomposition products : >150 °C small quantities of formaldehyde may be formed.
>280 °C danger of forming toxic fluorine-containing pyrolysis products.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Based on available data, the classification criteria are not met.

Product:

Acute oral toxicity : Remarks: This information is not available.

Acute inhalation toxicity : Remarks: This information is not available.

Acute dermal toxicity : Remarks: This information is not available.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version
3.6

Revision Date:
19.05.2025

Date of last issue: 22.08.2022
Date of first issue: 10.10.2014

Print Date:
19.05.2025

Skin corrosion/irritation

Based on available data, the classification criteria are not met.

Product:

Remarks : This information is not available.

Serious eye damage/eye irritation

Based on available data, the classification criteria are not met.

Product:

Remarks : This information is not available.

Respiratory or skin sensitisation

Skin sensitisation

Based on available data, the classification criteria are not met.

Respiratory sensitisation

Based on available data, the classification criteria are not met.

Product:

Remarks : This information is not available.

Germ cell mutagenicity

Based on available data, the classification criteria are not met.

Product:

Genotoxicity in vitro : Remarks: No data available

Genotoxicity in vivo : Remarks: No data available

Carcinogenicity

Based on available data, the classification criteria are not met.

Product:

Remarks : No data available

Reproductive toxicity

Based on available data, the classification criteria are not met.

Product:

Effects on fertility : Remarks: No data available

Effects on foetal development : Remarks: No data available

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version 3.6	Revision Date: 19.05.2025	Date of last issue: 22.08.2022 Date of first issue: 10.10.2014	Print Date: 19.05.2025
----------------	------------------------------	---	---------------------------

STOT - single exposure

Based on available data, the classification criteria are not met.

Product:

Remarks : No data available

STOT - repeated exposure

Based on available data, the classification criteria are not met.

Product:

Remarks : No data available

Repeated dose toxicity

Product:

Remarks : This information is not available.

Aspiration toxicity

Based on available data, the classification criteria are not met.

Product:

This information is not available.

Further information

Product:

Remarks : Information given is based on data on the components and the toxicology of similar products.

SECTION 12: Ecological information

12.1 Toxicity

Product:

Toxicity to fish : Remarks: No data available

Toxicity to daphnia and other aquatic invertebrates : Remarks: No data available

Toxicity to algae/aquatic plants : Remarks: No data available

Toxicity to microorganisms : Remarks: No data available

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

12.2 Persistence and degradability

Product:

Biodegradability : Remarks: No data available

Physico-chemical removability : Remarks: No data available

12.3 Bioaccumulative potential

Product:

Bioaccumulation : Remarks: No data available

12.4 Mobility in soil

Product:

Mobility : Remarks: No data available

Distribution among environmental compartments : Remarks: No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Other adverse effects

Product:

Endocrine disrupting potential : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Additional ecological information : No information on ecology is available.

Global warming potential

Assessment Report of the Intergovernmental Panel on Climate Change (IPCC) of the United Nations Framework Convention on Climate Change (UNFCCC)

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by
UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version 3.6	Revision Date: 19.05.2025	Date of last issue: 22.08.2022 Date of first issue: 10.10.2014	Print Date: 19.05.2025
----------------	------------------------------	---	---------------------------

Components:

octamethylcyclotetrasiloxane [D4]:

20-year global warming potential: 2.66
100-year global warming potential: 0.739
500-year global warming potential: 0.211
Atmospheric lifetime: 0.027 yr
Radiative efficiency: 0.12 Wm²ppb
Further information: Miscellaneous compounds

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- Product : The product should not be allowed to enter drains, water courses or the soil.
- Waste codes should be assigned by the user based on the application for which the product was used.
- Contaminated packaging : Packaging that is not properly emptied must be disposed of as the unused product.
Dispose of waste product or used containers according to local regulations.
- The following Waste Codes are only suggestions:
- Waste Code : used product, unused product
12 01 12*, spent waxes and fats
- uncleaned packagings
15 01 10*, packaging containing residues of or contaminated by hazardous substances

SECTION 14: Transport information

14.1 UN number or ID number

- ADR : Not regulated as a dangerous good
RID : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

14.2 UN proper shipping name

- ADR : Not regulated as a dangerous good
RID : Not regulated as a dangerous good

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by
UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version 3.6	Revision Date: 19.05.2025	Date of last issue: 22.08.2022 Date of first issue: 10.10.2014	Print Date: 19.05.2025
----------------	------------------------------	---	---------------------------

IMDG : Not regulated as a dangerous good

IATA : Not regulated as a dangerous good

14.3 Transport hazard class(es)

ADR : Not regulated as a dangerous good

RID : Not regulated as a dangerous good

IMDG : Not regulated as a dangerous good

IATA : Not regulated as a dangerous good

14.4 Packing group

ADR : Not regulated as a dangerous good

RID : Not regulated as a dangerous good

IMDG : Not regulated as a dangerous good

IATA (Cargo) : Not regulated as a dangerous good

IATA (Passenger) : Not regulated as a dangerous good

14.5 Environmental hazards

ADR : Not regulated as a dangerous good

RID : Not regulated as a dangerous good

IMDG : Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Maritime transport in bulk according to IMO instruments

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Relevant EU provisions transposed through retained EU law

UK REACH List of restrictions (Annex 17) : Not applicable

UK REACH Candidate list of substances of very high concern (SVHC) for Authorisation (UK SVHC) : This product does not contain substances of very high concern (UK: The REACH etc. (Amendment) Regulations, Article 57).

The Persistent Organic Pollutants Regulations (retained Regulation (EU) 2019/1021 as amended for Great : Not applicable

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

Britain)
(GB POPs)

Regulation (EU) No 2024/590 on substances that deplete the ozone layer (EC 2024/590) : Not applicable

Regulation (EU) 2019/1148 on the marketing and use of explosives precursors : Not applicable

UK REACH List of substances subject to authorisation (Annex XIV) (UK. REACH Annex XIV) : Not applicable

GB Export and import of hazardous chemicals - Prior Informed Consent (PIC) Regulation (GB PIC) : Not applicable

Control of Major Accident Hazards Regulations 2015 (COMAH) : Not applicable

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial and livestock rearing emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 0.06 %

15.2 Chemical safety assessment

This information is not available.

SECTION 16: Other information

Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - Agreement concerning the International Carriage of Dangerous Goods by Road; AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System;

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758 - GB



UNISILKON L 641

Version	Revision Date:	Date of last issue: 22.08.2022	Print Date:
3.6	19.05.2025	Date of first issue: 10.10.2014	19.05.2025

GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of very high concern; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

|| Relevant changes compared to the last edition are highlighted at the left margin. This version replaces all previous editions.

This safety data sheet applies only to products as originally packed and labelled. The information contained therein may not be reproduced or modified without our express written permission. Any forwarding of this document is only permitted to the extent required by law. Any further, in particular public, dissemination of the safety data sheet (e.g. as a document for download from the Internet) is not permitted without our express written consent. We provide our customers with amended safety data sheets as prescribed by law. The customer is responsible for passing on safety data sheets and any amendments contained therein to its own customers, employees and other users of the product. We provide no guarantee that safety data sheets received by users from third parties are up-to-date. All information and instructions in this safety data sheet have been compiled to the best of our knowledge and are based on the information available to us on the day of publication. The information provided is intended to describe the product in relation to the required safety measures; it is neither an assurance of characteristics nor a guarantee of the product's suitability for particular applications and does not justify any contractual legal relationship. The existence of a safety data sheet for a particular jurisdiction does not necessarily mean that import or use within that jurisdiction is legally permitted. If you have any questions, please contact your responsible sales contact or authorized trading partner.