



Safety Data Sheet

Chemie-Technik GmbH

according to UK REACH Regulation

GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 1 of 9

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

GLS 993 H1

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Lubricating agent

1.3. Details of the supplier of the safety data sheet

Company name: Chemie-Technik GmbH
ELKALUB Hochleistungs-Schmierstoffe
Street: Robert-Bosch-Straße 19
Place: D-72189 Vöhringen
Telephone: +49(0)7454 9652-0
e-mail: info@elkalub.com
Contact person: Cornelia Hölle
e-mail: cornelia.hoelle@elkalub.com
Internet: www.elkalub.com

Telephone: -25

1.4. Emergency telephone number:

Emergency CONTACT (24-Hour-Number): GBK GmbH +49 (0)6132-84463
National Health Service: 111 England/Wales (NHS Direct): 111 Scotland (NHS 24): 111



SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GB CLP Regulation

This mixture is not classified as hazardous in accordance with GB CLP Regulation.

2.2. Label elements

GB CLP Regulation

Special labelling of certain mixtures

EUH210 Safety data sheet available on request.

2.3. Other hazards

No information available.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

CAS No	Chemical name	Quantity
	EC No Index No REACH No	
	Classification (GB CLP Regulation)	
68411-46-1	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	0.1 - < 1 %
	270-128-1	
	Repr. 2, Aquatic Chronic 3; H361f H412	

Full text of H and EUH statements: see section 16.

Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity
		Specific Conc. Limits, M-factors and ATE	
68411-46-1	270-128-1	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	0.1 - < 1 %
		dermal: LD50 = > 2000 mg/kg; oral: LD50 = > 5000 mg/kg	



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 2 of 9

SECTION 4: First aid measures

4.1. Description of first aid measures

After inhalation

In case of inhalation of decomposition products, affected person should be moved into fresh air and kept still.

After contact with skin

Take off contaminated clothing and wash it before reuse.

After contact with skin, wash immediately with plenty of water and soap.

After contact with eyes

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist.

After ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing powder

Carbon dioxide (CO₂)

Foam

Unsuitable extinguishing media

Water spray jet

Water

5.2. Special hazards arising from the substance or mixture

Section 10

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Suppress gases/vapours/mists with water spray jet. Collect contaminated fire extinguishing water separately.

Do not allow entering drains or surface water.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General advice

Provide adequate ventilation. Do not breathe gas/fumes/vapour/spray. Avoid contact with skin, eyes and clothes. Use personal protection equipment.

Remove all sources of ignition.

6.2. Environmental precautions

Do not allow to enter into surface water or drains.

6.3. Methods and material for containment and cleaning up

Other information

Clean contaminated articles and floor according to the environmental legislation.



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 3 of 9

Treat the recovered material as prescribed in the section on waste disposal.

6.4. Reference to other sections

Safe handling: see section 7
Personal protection equipment: see section 8
Disposal: see section 13
Section 10: Stability and Reactivity

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

When using do not eat, drink or smoke.
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking.

Advice on general occupational hygiene

Remove contaminated, saturated clothing immediately. Draw up and observe skin protection programme.
Wash hands and face before breaks and after work and take a shower if necessary. When using do not eat, drink, smoke, sniff.

Further information on handling

After contact with skin, wash immediately with plenty of water and soap.
Advices on general occupational hygiene
Wash contaminated clothing prior to re-use.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep only in the original container in a cool, well-ventilated place.

Hints on joint storage

Combustible solids that cannot be assigned to any of the above storage classes

Further information on storage conditions

0 °C - 40 °C

7.3. Specific end use(s)

Lubricating agent

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
122-39-4	Diphenylamine	-	10		TWA (8 h)	WEL
		-	20		STEL (15 min)	WEL



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 4 of 9

DNEL/DMEL values

CAS No	Substance		
DNEL type	Exposure route	Effect	Value
68411-46-1	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene		
Worker DNEL, long-term	dermal	systemic	0,62 mg/kg bw/day
Consumer DNEL, long-term	oral	systemic	0,31 mg/kg bw/day
Consumer DNEL, long-term	inhalation	systemic	1,09 mg/m³
Consumer DNEL, long-term	dermal	systemic	0,31 mg/kg bw/day

PNEC values

CAS No	Substance		
Environmental compartment			Value
68411-46-1	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene		
Freshwater			0,051 mg/l
Marine water			0,0051 mg/l
Freshwater sediment			9320 mg/kg
Marine sediment			932 mg/kg
Soil			1860 mg/kg

8.2. Exposure controls



Individual protection measures, such as personal protective equipment

Eye/face protection

Suitable eye protection: goggles.

Hand protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. The quality of the protective gloves resistant to chemicals must be chosen as a function of the specific working place concentration and quantity of hazardous substances. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Skin protection

Use of protective clothing.

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Paste	
Colour:	white	
Melting point/freezing point:		No data available
Boiling point or initial boiling point and boiling range:		No data available



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 5 of 9

Flammability:	No data available
Lower explosion limits:	No data available
Upper explosion limits:	No data available
Flash point:	No data available
Auto-ignition temperature:	No data available
Decomposition temperature:	No data available
pH-Value:	No data available
Viscosity / kinematic:	No data available
Water solubility:	practically insoluble
Solubility in other solvents	
not determined	
Partition coefficient n-octanol/water:	No data available
Vapour pressure:	< 0,0001 hPa
(at 20 °C)	
Density (at 25 °C):	0,93 g/cm ³
Bulk density:	No data available
Relative vapour density:	not determined

9.2. Other information

Information with regard to physical hazard classes

Explosive properties

The product is not: Explosive.

Sustaining combustion:

No data available

Self-ignition temperature

Solid:

No data available

Gas:

No data available

Oxidizing properties

Not oxidising.

Other safety characteristics

Evaporation rate:

not determined

Solid content:

not determined

Sublimation point:

No data available

Softening point:

No data available

Pour point:

No data available

Viscosity / dynamic:

No data available

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reaction when handled and stored according to provisions.

10.2. Chemical stability

The product is chemically stable under recommended conditions of storage, use and temperature.

10.3. Possibility of hazardous reactions

The product is chemically stable under recommended conditions of storage, use and temperature.

10.4. Conditions to avoid

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

10.5. Incompatible materials

Oxidizing agent

10.6. Hazardous decomposition products

Carbon monoxide, Carbon dioxide



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 6 of 9

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in GB CLP Regulation

Acute toxicity

Based on available data, the classification criteria are not met.

ATEmix tested

	Dose	Species	Source
LD50, oral	> 2000 mg/kg		
LD50, dermal	> 2000 mg/kg		

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
68411-46-1	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene				
	oral	LD50 > 5000 mg/kg	Rat		
	dermal	LD50 > 2000 mg/kg	Rat		

Irritation and corrosivity

Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

Additional information on tests

The mixture is classified as hazardous according to regulation (EC) No 1272/2008 [CLP].

11.2. Information on other hazards

Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to humans as no components meets the criteria.

SECTION 12: Ecological information

12.1. Toxicity

The product is not: Ecotoxic.

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h] [d]	Species	Source	Method
68411-46-1	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene					
	Acute crustacea toxicity	EC50 10 mg/l	48 h	Daphnia magna (Big water flea)		

12.2. Persistence and degradability

No data available

12.3. Bioaccumulative potential



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 7 of 9

No data available

12.4. Mobility in soil

No data available

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

No data available

12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

No data available

12.7. Other adverse effects

No information available.

Further information

Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal recommendations

Do not allow to enter into surface water or drains.

Dispose of waste according to "Kreislaufwirtschaftsgesetz (KrWG)".

Dispose of waste according to applicable legislation.

The waste key according to the European Waste Catalogue (EWC number) refers to the real wastes origin and therefore is not product- but use-oriented.

Consult the appropriate local waste disposal expert about waste disposal.

List of Wastes Code - residues/unused products

120112 WASTES FROM SHAPING AND PHYSICAL AND MECHANICAL SURFACE TREATMENT OF METALS AND PLASTICS; wastes from shaping and physical and mechanical surface treatment of metals and plastics; spent waxes and fats; hazardous waste

List of Wastes Code - used product

120112 WASTES FROM SHAPING AND PHYSICAL AND MECHANICAL SURFACE TREATMENT OF METALS AND PLASTICS; wastes from shaping and physical and mechanical surface treatment of metals and plastics; spent waxes and fats; hazardous waste

List of Wastes Code - contaminated packaging

150110 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); packaging containing residues of or contaminated by hazardous substances; hazardous waste

Contaminated packaging

Wash with plenty of water. Completely emptied packages can be recycled.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

14.4. Packing group:

No dangerous good in sense of this transport regulation.

Inland waterways transport (ADN)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 8 of 9

14.4. Packing group:

No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

14.4. Packing group:

No dangerous good in sense of this transport regulation.

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number or ID number:

No dangerous good in sense of this transport regulation.

14.2. UN proper shipping name:

No dangerous good in sense of this transport regulation.

14.3. Transport hazard class(es):

No dangerous good in sense of this transport regulation.

14.4. Packing group:

No dangerous good in sense of this transport regulation.

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No

14.6. Special precautions for user

No dangerous good in sense of this transport regulation.

Section 7: Handling and Storage

Section 8: Exposure Controls/Personal Protection

14.7. Maritime transport in bulk according to IMO instruments

No information available.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

Restrictions on use (REACH, annex XVII):

Entry 75

Information according to 2012/18/EU
(SEVESO III):

Not subject to 2012/18/EU (SEVESO III)

National regulatory information

Employment restrictions:

Observe restrictions to employment for juveniles according to the 'juvenile work protection guideline' (94/33/EC).

Water hazard class (D):

1 - slightly hazardous to water

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Changes

This data sheet contains changes from the previous version in section(s): 2.

Abbreviations and acronyms

CLP: Classification, labelling and Packaging

REACH: Registration, Evaluation and Authorization of Chemicals

GHS: Globally Harmonised System of Classification, Labelling and Packaging of Chemicals

UN: United Nations

CAS: Chemical Abstracts Service

DNEL: Derived No Effect Level

DMEL: Derived Minimal Effect Level

PNEC: Predicted No Effect Concentration

ATE: Acute toxicity estimate

LC50: Lethal concentration, 50%

LD50: Lethal dose, 50%



GLS 993 H1

Revision date: 10.02.2023

Product code: G0993H1X

Page 9 of 9

LL50: Lethal loading, 50%
EL50: Effect loading, 50%
EC50: Effective Concentration 50%
ErC50: Effective Concentration 50%, growth rate
NOEC: No Observed Effect Concentration
BCF: Bio-concentration factor
PBT: persistent, bioaccumulative, toxic
vPvB: very persistent, very bioaccumulative
ADR: Accord européen sur le transport des marchandises dangereuses par Route
(European Agreement concerning the International Carriage of Dangerous Goods by Road)
RID: Regulations concerning the international carriage of dangerous goods by rail
ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
(Accord européen relatif au transport international des marchandises dangereuses par voies de navigation
intérieures)
IMDG: International Maritime Code for Dangerous Goods
EmS: Emergency Schedules
MFAG: Medical First Aid Guide
IATA: International Air Transport Association
ICAO: International Civil Aviation Organization
MARPOL: International Convention for the Prevention of Marine Pollution from Ships
IBC: Intermediate Bulk Container
SVHC: Substance of Very High Concern
For abbreviations and acronyms, see table at <http://abbrev.esdscom.eu>

Relevant H and EUH statements (number and full text)

H361f	Suspected of damaging fertility.
H412	Harmful to aquatic life with long lasting effects.
EUH210	Safety data sheet available on request.

Further Information

The information is based on the present level of our knowledge. It does not, however, give assurance of product properties and establishes no contract legal rights. The receiver of our product is singularly responsible for adhering to existing laws and regulations.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)