

SAFETY DATA SHEET

according to GB/T 16483 and GB/T 17519CN

KLÜBER
LUBRICATION

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

1. PRODUCT AND COMPANY IDENTIFICATION

Product name : Klüberplex BE 31-102 润滑脂
Article-No. : 017135
Chemical nature : special calcium soap
Mineral oil.

Manufacturer or supplier's details

Company name of supplier : Klüber Lubrication München GmbH & Co. KG
Geisenhausenerstr. 7
81379 München
Deutschland
Tel.: +49 (0) 89 7876 0
Fax: +49 (0) 89 7876 333
info@klueber.com

E-mail address of person responsible for the SDS : mcm@klueber.com

National contact : Klüber Lubrication (Shanghai) Co., Ltd.
No.88 Tuo Qing Road
Qingpu Industrial Zone
Shanghai 201700
China
Phone: +86 21 69225666
Email: info@cn.klueber.com
www.klueber.com.cn

Klüberplex BE 31-102=
LUB-KB1
Festo SE&Co. KG
Ruiter Strasse 82
D-73734 Esslingen
www.Festo.com/en/msds

Klüber Lubrication China Limited
Room 1012 Shatin Galleria
18-24 Shan Mei Street, Fotan, Shatin, N.T.
Hong Kong
China
Phone: +852 26920191
Email: info@cn.klueber.com
www.klueber.com.cn

Emergency telephone number : +86 532 8388 9090 (NRCC, only for hazardous chemicals)
+86 21 69225521

Recommended use of the chemical and restrictions on use

Recommended use : Grease
Restrictions on use : Restricted to professional users.

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance : paste
Colour : brown
Odour : characteristic

Not a hazardous substance or mixture.

GHS Classification

Not a hazardous substance or mixture.

GHS label elements

Not a hazardous substance or mixture.

Physical and chemical hazards

Not classified based on available information.

Health hazards

Not classified based on available information.

Environmental hazards

Not classified based on available information.

Other hazards which do not result in classification

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide	1282612-32-1	>= 20 -< 30

4. FIRST AID MEASURES

If inhaled : Remove person to fresh air. If signs/symptoms continue, get medical attention.
Keep patient warm and at rest.
If breathing is irregular or stopped, administer artificial respiration.

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

- In case of skin contact : Remove contaminated clothing. If irritation develops, get medical attention.
Wash off with soap and water.
- In case of eye contact : Rinse immediately with plenty of water, also under the eyelids, for at least 10 minutes.
If eye irritation persists, consult a specialist.
- If swallowed : Move the victim to fresh air.
Do not induce vomiting without medical advice.
- Most important symptoms and effects, both acute and delayed : No symptoms known or expected.
- Notes to physician : Treat symptomatically.

5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
- Unsuitable extinguishing media : High volume water jet
- Hazardous combustion products : Carbon oxides
Nitrogen oxides (NOx)
Metal oxides
- Specific extinguishing methods : Standard procedure for chemical fires.
- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.
Exposure to decomposition products may be a hazard to health.

6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Evacuate personnel to safe areas.
Do not breathe vapours, aerosols.
Refer to protective measures listed in sections 7 and 8.
- Environmental precautions : Try to prevent the material from entering drains or water courses.
Local authorities should be advised if significant spillages cannot be contained.

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Methods and materials for containment and cleaning up : Pick up and transfer to properly labelled containers.

7. HANDLING AND STORAGE

Handling

Advice on safe handling : For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Wash hands and face before breaks and immediately after handling the product.

Avoidance of contact : No materials to be especially mentioned.

Storage

Conditions for safe storage : Store in original container.
Keep container closed when not in use.
Keep in a dry, cool and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Store in accordance with the particular national regulations.
Keep in properly labelled containers.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Distillates (petroleum), hydrotreated heavy paraffinic	64742-54-7	TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH (2013-03-01)
Distillates (petroleum), solvent-dewaxed heavy paraffinic	64742-65-0	TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH (2013-03-01)
White mineral oil (petroleum)	8042-47-5	TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH (2013-03-01)

Engineering measures : none

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Personal protective equipment

- Respiratory protection : Not required; except in case of aerosol formation.
- Filter type : Filter type P
- Eye/face protection : Safety glasses
- Skin and body protection : Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.
- Hand protection
- Material : Nitrile rubber
- Break through time : > 10 min
- Protective index : Class 1
- Remarks : For prolonged or repeated contact use protective gloves. The break through time depends amongst other things on the material, the thickness and the type of glove and therefore has to be measured for each case.
- Protective measures : The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.
- Hygiene measures : Wash face, hands and any exposed skin thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : paste
- Colour : brown
- Odour : characteristic
- Odour Threshold : No data available
- pH : Not applicable
- Melting point/ range : No data available

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Boiling point/boiling range : No data available

Flash point : Not applicable

Evaporation rate : No data available

Flammability (solid, gas) : Combustible Solids

Self-ignition : No data available

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : < 0.001 hPa (20 °C)

Relative vapour density : No data available

Relative density : 0.96 (20 °C)
Reference substance: Water
The value is calculated

Density : 0.96 g/cm³ (20 °C)

Bulk density : No data available

Solubility(ies)
Water solubility : insoluble

Solubility in other solvents : No data available

Partition coefficient: n-octanol/water : No data available

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity
Viscosity, dynamic : No data available

Viscosity, kinematic : Not applicable

Explosive properties : Not explosive

Oxidizing properties : No data available

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Sublimation point : No data available
Particle size : Not applicable

10. STABILITY AND REACTIVITY

Reactivity : No hazards to be specially mentioned.
Chemical stability : Stable under normal conditions.
Possibility of hazardous reactions : No dangerous reaction known under conditions of normal use.
Conditions to avoid : No conditions to be specially mentioned.
Incompatible materials : No materials to be especially mentioned.
Hazardous decomposition products : No decomposition if stored and applied as directed.

11. TOXICOLOGICAL INFORMATION

Acute toxicity

Based on available data, the classification criteria are not met.

Product:

Acute oral toxicity : Acute toxicity estimate: > 5,000 mg/kg
Method: Calculation method

Acute inhalation toxicity : Remarks: This information is not available.

Acute dermal toxicity : Acute toxicity estimate: > 5,000 mg/kg
Method: Calculation method

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Method: Directive 67/548/EEC, Annex V, B.1.
GLP: yes

SAFETY DATA SHEET

according to GB/T 16483 and GB/T 17519CN

KLÜBER
LUBRICATION

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Acute dermal toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 402
GLP: yes

Skin corrosion/irritation

Based on available data, the classification criteria are not met.

Product:

Remarks : This information is not available.

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Species : Rabbit
Assessment : No skin irritation
Method : OECD Test Guideline 404
Result : No skin irritation
GLP : yes

Serious eye damage/eye irritation

Based on available data, the classification criteria are not met.

Product:

Remarks : This information is not available.

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Species : Rabbit
Result : No eye irritation
Assessment : No eye irritation
Method : OECD Test Guideline 405
GLP : yes

Respiratory or skin sensitisation

Skin sensitisation

Based on available data, the classification criteria are not met.

Respiratory sensitisation

Based on available data, the classification criteria are not met.

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Product:

Remarks : This information is not available.

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Test Type : Maximisation Test
Species : Guinea pig
Assessment : Does not cause skin sensitisation.
Method : OECD Test Guideline 406
Result : Does not cause skin sensitisation.
GLP : yes

Germ cell mutagenicity

Based on available data, the classification criteria are not met.

Product:

Genotoxicity in vitro : Remarks: No data available

Genotoxicity in vivo : Remarks: No data available

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Genotoxicity in vitro : Test Type: Ames test
Method: Mutagenicity (Escherichia coli - reverse mutation assay)
Result: negative
GLP: yes

Carcinogenicity

Based on available data, the classification criteria are not met.

Product:

Remarks : No data available

Reproductive toxicity

Based on available data, the classification criteria are not met.

Product:

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Effects on fertility : Remarks: No data available

Effects on foetal development : Remarks: No data available

STOT - single exposure

Based on available data, the classification criteria are not met.

Product:

Remarks : No data available

STOT - repeated exposure

Based on available data, the classification criteria are not met.

Product:

Remarks : No data available

Repeated dose toxicity

Product:

Remarks : This information is not available.

Aspiration toxicity

Based on available data, the classification criteria are not met.

Product:

This information is not available.

Further information

Product:

Remarks : Information given is based on data on the components and the toxicology of similar products.

SAFETY DATA SHEET

according to GB/T 16483 and GB/T 17519CN

KLÜBER
LUBRICATION

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Physico-chemical
removability : Remarks: No data available

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Biodegradability : Primary biodegradation
Inoculum: activated sludge
Result: Not rapidly biodegradable
Biodegradation: 26.1 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
GLP: yes

Bioaccumulative potential

Product:

Bioaccumulation : Remarks: No data available

Components:

Reaction mixture of hydrogenated tallow alkyl amines with sebacic acid and calcium hydroxide:

Partition coefficient: n-
octanol/water : log Pow: 0.9 - 18

Mobility in soil

Product:

Mobility : Remarks: No data available

Distribution among
environmental compartments : Remarks: No data available

Other adverse effects

Product:

Additional ecological
information : No information on ecology is available.

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

13. DISPOSAL CONSIDERATIONS

Disposal methods

- Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
- Contaminated packaging : Packaging that is not properly emptied must be disposed of as the unused product.
Dispose of waste product or used containers according to local regulations.

14. TRANSPORT INFORMATION

International Regulations

UNRTDG

- UN number : Not applicable
Proper shipping name : Not applicable
Class : Not applicable
Subsidiary risk : Not applicable
Packing group : Not applicable
Labels : Not applicable

IATA-DGR

- UN/ID No. : Not applicable
Proper shipping name : Not applicable
Class : Not applicable
Subsidiary risk : Not applicable
Packing group : Not applicable
Labels : Not applicable
Packing instruction (cargo aircraft) : Not applicable
Packing instruction (passenger aircraft) : Not applicable

IMDG-Code

- UN number : Not applicable
Proper shipping name : Not applicable
Class : Not applicable
Subsidiary risk : Not applicable
Packing group : Not applicable
Labels : Not applicable
EmS Code : Not applicable
Marine pollutant : Not applicable

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

National Regulations

Klüberplex BE 31-102 润滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

GB 6944/12268

UN number : Not applicable
Proper shipping name : Not applicable
Class : Not applicable
Subsidiary risk : Not applicable
Packing group : Not applicable
Labels : Not applicable

Special precautions for user

Not applicable

15. REGULATORY INFORMATION

National regulatory information

Law on the Prevention and Control of Occupational Diseases

Regulations on Safety Management of Hazardous Chemicals

Catalogue of Hazardous Chemicals : This product is not listed in the catalogue of hazardous chemicals and it does not meet the definition of hazardous chemicals and its principles of determination.

Identification of Major Hazard Installations for Hazardous Chemicals (GB 18218) : Not listed

Hazardous Chemicals for Priority Management under SAWS : Not listed

Catalogue of Specially Controlled Hazardous Chemicals : Not listed

List of Explosive Precursors : Not listed

Regulations on Labour Protection in Workplaces where Toxic Substances are Used

Catalogue of Highly Toxic Chemicals : Not listed

Regulation of Environmental Management on the First Import of Chemicals and the Import and Export of Toxic Chemicals

China Severely Restricted Toxic Chemicals : Not listed

Regulation on the Administration of Precursor Chemicals

Catalogue and Classification of Precursor Chemicals : Not listed

Regulations of Ozone Depleting Substances Management

SAFETY DATA SHEET

according to GB/T 16483 and GB/T 17519CN

KLÜBER
LUBRICATION

Klüberplex BE 31-102 潤滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

List of Controlled Ozone Depleting Substances : Not listed

List of Controlled Ozone Depleting Substances Import and Export : Not listed

Environmental Protection Law

List of Priority Controlled Chemicals : Not listed

List of Key Controlled New Pollutants : Not listed

Montreal Protocol : Not applicable

Rotterdam Convention (Prior Informed Consent) : Not applicable

Stockholm Convention (Persistent Organic Pollutants) : Not applicable

The components of this product are reported in the following inventories:

IECSC : On the inventory, or in compliance with the inventory

16. OTHER INFORMATION

Date format : yyyy/mm/dd

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)

ACGIH / TWA : 8-hour, time-weighted average

AIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No

SAFETY DATA SHEET

according to GB/T 16483 and GB/T 17519CN



Klüberplex BE 31-102 潤滑脂

Version 1.10 Revision Date: 2025-06-30 Date of last issue: 2024-05-28
Date of first issue: 2015-06-25 Print Date: 2025-06-30

Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECl - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

|| Relevant changes compared to the last edition are highlighted at the left margin. This version replaces all previous editions.

Disclaimer

This safety data sheet applies only to products as originally packed and labelled. The information contained therein may not be reproduced or modified without our express written permission. Any forwarding of this document is only permitted to the extent required by law. Any further, in particular public, dissemination of the safety data sheet (e.g. as a document for download from the Internet) is not permitted without our express written consent. We provide our customers with amended safety data sheets as prescribed by law. The customer is responsible for passing on safety data sheets and any amendments contained therein to its own customers, employees and other users of the product. We provide no guarantee that safety data sheets received by users from third parties are up-to-date. All information and instructions in this safety data sheet have been compiled to the best of our knowledge and are based on the information available to us on the day of publication. The information provided is intended to describe the product in relation to the required safety measures; it is neither an assurance of characteristics nor a guarantee of the product's suitability for particular applications and does not justify any contractual legal relationship. The existence of a safety data sheet for a particular jurisdiction does not necessarily mean that import or use within that jurisdiction is legally permitted. If you have any questions, please contact your responsible sales contact or authorized trading partner.