


Semi-rotary drive DSM-T-12-270-P-FW-A-B

Part number: 1145087

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Size | 12 |
| Cushioning angle | 1.8 deg |
| Rotation angle adjustment range | 0 deg ... 270 deg |
| Swivel angle | 0 deg ... 270 deg |
| Permissible stop radius | ≥15 mm |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Fine adjustment | -6 deg |
| Mode of operation | Double-acting |
| Design | Vane |
| Position detection | Via proximity switch |
| Symbol | 00991265 |
| Operating pressure | 0.25 MPa ... 1 MPa |
| Operating pressure | 2.5 bar ... 10 bar |
| Max. swivel frequency at 0.6 MPa (6 bar, 87 psi) | 2 Hz |
| Repetition accuracy | 1 deg |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. stop force | 90 N |
| Max. axial force | 18 N |
| Max. radial force | 45 N |
| Theoretical torque at 0.6 MPa (6 bar, 87 psi) | 2.5 Nm |
| Permissible mass moment of inertia | 0.005 kgm ² |
| Product weight | 383 g |
| Type of mounting | Via female thread |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Material drive shaft | Steel Nickel-plated |
| Material seals | TPE-U(PU) |
| Material housing | Anodised aluminium |