

Solenoid valve MFH-3-3/4

Part number: 11967

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Valve function | 3/2-way, closed, monostable |
| Type of actuation | Electric |
| Construction width | 68 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 7500 l/min |
| pneumatic working port | G3/4 |
| Operating voltage | Via solenoid coil, must be ordered separately |
| Operating pressure | 0.2 MPa ... 0.8 MPa |
| Operating pressure | 2 bar ... 8 bar |
| Design | Poppet seat |
| Type of reset | Mechanical spring |
| Approval | c UL us - Recognized (OL) |
| Degree of protection | IP65 |
| Nominal size | 19 mm |
| Exhaust-air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | optional |
| Manual override | Detenting |
| Type of piloting | Pilot actuated |
| Pilot air supply | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991008 |
| lap | Underlap |
| Switching time off | 32 ms |
| Switching time on | 36 ms |
| Max. positive test pulse with 0 signal | 2200 µs |
| Characteristic coil data | See solenoid coil, to be ordered separately |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 60 °C |
| Media temperature | -10 °C ... 60 °C |
| Ambient temperature | -5 °C ... 40 °C |
| Product weight | 1260 g |
| Electrical connection | Via F coil, to be ordered separately |

| Feature | Value |
|------------------------------|---------------------------------------|
| Type of mounting | On manifold rail With through-hole |
| Pilot exhaust port 82 | M5 |
| Pneumatic connection, port 1 | G3/4 |
| Pneumatic connection, port 2 | G3/4 |
| Pneumatic connection, port 3 | G3/4 |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material housing | Die-cast aluminium |