

# Angle gripper DHWS-16-A-NC

Part number: 1310179

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	16
Max. replacement accuracy	≤0.2 mm
Max. opening angle	40 deg
Rotationally symmetrical	≤0.2 mm
Repetition accuracy, gripper	≤0.04 mm
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Bracket
Gripper force back-up	During closing
Design	Lever
Position detection	Via proximity switch
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Max. operating frequency of gripper	≤4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	62 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	36 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils.
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	0.15 kgcm <sup>2</sup>
Max. force on gripper jaw Fz static	50 N
Max. torque at gripper Mx static	1.6 Nm
Max. torque at gripper My static	1.6 Nm
Max. torque at gripper Mz static	1.6 Nm
Product weight	114 g
Type of mounting	Either: Via female thread and centring sleeve Via through-hole and centring sleeve
Pneumatic connection	M3
Note on materials	RoHS compliant

<b>Feature</b>	<b>Value</b>
Material cover cap	Process automation
Material housing	Wrought aluminium alloy Hard anodised
Material gripper jaws	High-alloy steel