

Solenoid valve

VZWP-L-M22C-N34-250-V-1P4-40

FESTO

Part number: 1489978



 General operating condition

Data sheet

Feature	Value
Design	Piloted piston poppet valve
Type of actuation	Electrical
Sealing principle	Soft
Mounting position	Coil on top (preferred)
Type of mounting	Inline installation
Connection Process valve	3/4 NPT
Electrical connection	Plug To EN 175301-803 Square design
Nominal size	25 mm
Valve function	2/2-way, single solenoid, closed
Manual override	None
Flow direction	Non-reversible
Medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases Neutral fluids Other media on request
Nominal pressure PN	40
Pressure difference	0.05 MPa
Pressure difference	0.5 bar
Pressure difference	7.25 psi
Characteristic coil data	24 V DC: 6.8 W
Insulation material class	H
Permissible voltage fluctuations	+/-10%
Duty cycle	100%
Type of piloting	Piloted
Symbol	00992974
Medium pressure	0.05 MPa ... 4 MPa
Medium pressure	0.5 bar ... 40 bar
Medium pressure	7.25 psi ... 580 psi
Max. viscosity	22 mm ² /s

Feature	Value
Media temperature	-10 °C ... 80 °C
Ambient temperature	-10 °C ... 35 °C
Leakage rate to EN 12266-1	A
Flow rate Kv	8.2 m³/h
Standard nominal flow rate (standardised to DIN 1343)	8750 l/min
Switching time on	130 ms
Switching time off	300 ms
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Cast brass
Material number housing	CW617N
Material seals	Fluoro rubber
Material screws	High-alloy stainless steel
Material number screw	1,4301
Product weight	1500 g
Degree of protection	IP65
Corrosion resistance class CRC	1 - Low corrosion stress