

# Solenoid valve

## VZWF-L-M22C-N112-400-E-3AP4-10

FESTO

Part number: 1492372



[PDF](#) General operating condition

## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Design                           | Diaphragm valve<br>Force pilot operated  |
| Type of actuation                | Electric   |
| Sealing principle                | Soft   |
| Mounting position                | Solenoid vertical  |
| Type of mounting                 | In-line installation   |
| Connection Process valve         | 1 1/2 NPT  |
| Electrical connection            | Plugs<br>To EN 175301-803<br>Square design   |
| Nominal size                     | 40 mm  |
| Valve function                   | 2/2-way, closed, monostable  |
| Manual override                  | None   |
| Flow direction                   | Non-reversible   |
| Medium                           | Compressed air to ISO 8573-1:2010 [7:-:-]<br>Inert gases<br>Mineral oil<br>Water<br>Neutral fluids<br>Other media on request |
| Nominal pressure PN              | 40   |
| Pressure difference              | 0 MPa  |
| Pressure difference              | 0 bar  |
| Pressure difference              | 0 psi  |
| Characteristic coil data         | 230 V AC: 50/60 Hz, pick-up power 30.0 VA, holding power 30.0 VA   |
| Permissible voltage fluctuations | +/- 10 %   |
| Symbol                           | 00992976   |
| Medium pressure                  | 0 MPa ... 1 MPa  |
| Medium pressure                  | 0 bar ... 10 bar   |
| Medium pressure                  | 0 psi ... 145 psi  |
| Max. viscosity                   | 22 mm <sup>2</sup> /s  |
| Media temperature                | -10 °C ... 80 °C   |

| <b>Feature</b>  | <b>Value</b>  |
|---|---|
| Ambient temperature                                   | -10 °C ... 35 °C  |
| Leakage rate to EN 12266-1                            | A   |
| Flow rate Kv  | 22.5 m³/h   |
| Standard nominal flow rate (standardised to DIN 1343) | 23500 l/min   |
| Switching time on                                     | 620 ms  |
| Switching time off                                    | 1140 ms   |
| Note on materials                                     | RoHS-compliant  |
| LABS (PWIS) conformity                                | VDMA24364 zone III  |
| Material housing                                      | Cast brass  |
| Material number housing                               | CW617N  |
| Material seals  | EPDM  |
| Material screws                                       | High-alloy stainless steel  |
| Material number screw                                 | 1.4301  |
| Product weight  | 4500 g  |
| CE mark (see declaration of conformity)               | In accordance with EU Pressure Equipment Directive<br>To EU Low Voltage Directive |
| UKCA marking (see declaration of conformity)          | To UK regulations for electrical equipment  |
| Degree of protection                                  | IP65  |
| Corrosion resistance class CRC                        | 1 - Low corrosion stress  |