

# Pneumatic valve VL-5/3B-3/8-B

Part number: 14951

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | 5/3-way, pressurised   |
| Type of actuation                                     | Pneumatic  |
| Construction width                                    | 40 mm  |
| Standard nominal flow rate (standardised to DIN 1343) | 2600 l/min   |
| pneumatic working port                                | G3/8   |
| Operating pressure                                    | -0.09 MPa ... 1 MPa  |
| Operating pressure                                    | -0.9 bar ... 10 bar  |
| Design  | Piston gate valve  |
| Type of reset   | Mechanical spring  |
| Nominal size  | 12 mm  |
| Grid dimension  | 41 mm  |
| Exhaust-air function                                  | With flow control option   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | optional   |
| Manual override                                       | None   |
| Type of piloting                                      | Direct   |
| Pilot air supply                                      | External   |
| Flow direction  | Reversible   |
| Symbol  | 00991022   |
| lap   | Overlap  |
| Pilot pressure  | 0.3 MPa ... 1 MPa  |
| Pilot pressure  | 3 bar ... 10 bar   |
| Max. switching frequency                              | 3 Hz   |
| Switching time off                                    | 28 ms  |
| Switching time on                                     | 7 ms   |
| Switching time reversal                               | 78 ms  |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                        | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L  |
| Storage temperature                                   | -40 °C ... 60 °C   |
| Media temperature                                     | -10 °C ... 60 °C   |
| Pilot medium  | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Ambient temperature                                   | -10 °C ... 60 °C   |
| Product weight  | 680 g  |

| <b>Feature</b>               | <b>Value</b>                    |
|------------------------------|---------------------------------|
| Type of mounting             | On PR rail<br>With through-hole |
| Pilot air port 12            | G1/8                            |
| Pilot air port 14            | G1/8                            |
| Pneumatic connection, port 1 | G3/8                            |
| Pneumatic connection, port 2 | G3/8                            |
| Pneumatic connection, port 3 | G3/8                            |
| Pneumatic connection, port 4 | G3/8                            |
| Pneumatic connection, port 5 | G3/8                            |
| Note on materials            | RoHS-compliant                  |
| Material seals               | NBR                             |
| Material housing             | Die-cast aluminium              |