


Proximity sensor SIEN-M18B-PS-K-L

Part number: 150418

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Symbol	00991702
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	according to UK RoHS instructions (UK-R)
Note on materials	RoHS-compliant
Rated operating distance	5 mm
Assured operating distance	4.05 mm
Reduction factors	Aluminium = 0.4 Stainless steel St 18/8 = 0.8 Copper = 0.4 Brass = 0.5 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy	0.25 mm
Switching output	PNP
Switching element function	N/O contact
Hysteresis	≤0.55 mm
Max. switching frequency	2000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V ... 30 V
Residual ripple	+/- 20 %
No-load supply current	≤10 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Cable
Electrical connection 1, connector system	Open end
Electrical connection 1, number of connections/cores	3
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Size	M18x1
Type of mounting	Via lock nut
Tightening torque	20 Nm
Mounting type	Flush

Feature	Value
Product weight	108 g
Material housing	PBTP Nickel-plated
Switching status indication	Yellow LED
Ambient temperature with moving cable	-5 °C ... 70 °C
Degree of protection	IP67
LABS (PWIS) conformity	VDMA24364-B2-L
Pollution degree	3
Additional information for sensor selection	with standard sensing distance
Electrical output	PNP
Selection of sensor design	Standard