

Proximity sensor SIES-V3B-NS-S-L

Part number: 150490

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Symbol	00991703
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Rated operating distance	2 mm
Assured operating distance	1.6 mm
Reduction factors	Aluminium = 0.45 Stainless steel St 18/8 = 0.7 Copper = 0.3 Brass = 0.5 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 85 °C
Repetition accuracy	0.1 mm
Switching output	NPN
Switching element function	N/O contact
Max. switching frequency	1200 Hz
Max. switching frequency DC	1200 Hz
Max. output current as a function of temperature	200 mA at ≤ 50 °C 150 mA at ≤ 85 °C
Voltage drop	3.2 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V ... 30 V
Residual ripple	10 %
No-load supply current	≤30 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	3
Electrical connection 1, type of mounting	Not rotatable
Electrical connection 1, compatible type of mounting	Compatible with latching lock Compatible with rotatable screw-type lock
Size	15x20x30 mm
Type of mounting	With through-hole
Mounting type	Flush
Product weight	120 g

Feature	Value
Material housing	Die-cast zinc
Switching status indication	Yellow LED
Degree of protection	IP67
LABS (PWIS) conformity	VDMA24364-B2-L
Additional information for sensor selection	Special design
Electrical output	NPN
Selection of sensor design	Standard