

Condensate drain WA-2

Part number: 152810

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|-----------------------------|---------------------------------------|
| Type of actuation | Mechanical |
| Mounting position | Vertical +/-5° |
| Manual override | Non-detenting |
| Condensate drain | Fully automatic |
| Design | External, mechanical, fully automatic |
| Measured variable | Level |
| Valve function | 2/2 open, monostable |
| Operating pressure | 1.5 bar ... 14 bar |
| Operating medium | Water |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -20 °C ... 60 °C |
| Media temperature | 0 °C ... 50 °C |
| Ambient temperature | 0 °C ... 50 °C |
| Product weight | 92 g |
| Type of mounting | In-line installation |
| Condensate drain connection | PK-4 |
| Pneumatic connection | M9 |
| Material housing | Wrought aluminium alloy |