

Compact cylinder ADVUL-20-40-P-A

Part number: 156864

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|--|--|
| Stroke | 40 mm |
| Piston diameter | 20 mm |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Design | Piston Piston rod |
| Position detection | Via proximity switch |
| Symbol | 00991737 |
| Variants | Piston rod at one end |
| Protection against torque/guide | Guide rod with yoke |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in end positions | 0.14 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 141 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 188 N |
| Moving mass for 0 mm stroke | 50 g |
| Additional moving mass per 10 mm stroke | 11 g |
| Basic weight for 0 mm stroke | 179 g |
| Additional weight per 10 mm stroke | 26 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection | M5 |
| Material collar screws | Galvanised steel |
| Material cover | Wrought aluminium alloy |
| Material dynamic seals | NBR TPE-U(PU) |
| Material piston rod | High-alloy stainless steel |
| Material cylinder barrel | Wrought aluminium alloy |