

Fine filter LFMB-1/8-D-MINI-A

Part number: 162634

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Series | D |
| Size | Mini |
| Design | Fibre filter |
| Grade of filtration | 1 µm |
| Condensate drain | Fully automatic |
| Symbol | 00991520 |
| Operating pressure | 2 bar ... 12 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [6:8:4] Inert gas |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [5:7:3] Inert gas |
| Max. standard flow rate for clean air class | 500 l/min |
| Min. standard flow rate for clean air class | 150 l/min |
| Filter efficiency | 99.99 % |
| Max. condensate volume | 22 ml |
| Bowl guard | Metal bowl guard |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | 1.5 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Storage temperature | -10 °C ... 60 °C |
| Residual oil content | 0.5 mg/m ³ |
| Type of mounting | With accessories |
| Mounting position | Vertical +/-5° |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Material housing | Die-cast zinc |
| Material filter | Borosilicate fibre |
| Material bowl | Makrolon® |
| Note on materials | RoHS compliant |
| Product weight | 250 g |