

# Solenoid valve CPE24-M1H-30L-QS-10

Part number: 163172

FESTO



[PDF General operating condition](#)

## Data sheet

| Feature   | Value                                     |
|---|---|
| Valve function  | 3/2 open, monostable                      |
| Type of actuation                                     | Electric                                  |
| Construction width                                    | 24 mm                                     |
| Standard nominal flow rate (standardised to DIN 1343) | 1250 l/min                                |
| pneumatic working port                                | QS-10                                     |
| Operating voltage                                     | 24V DC                                    |
| Operating pressure                                    | 0.25 MPa ... 1 MPa                        |
| Operating pressure                                    | 2.5 bar ... 10 bar                        |
| Design  | Piston gate valve                         |
| Type of reset   | Pneumatic spring                          |
| Approval  | c UL us - Recognized (OL)                 |
| Maritime classification                               | See certificate                           |
| Certificate issuing authority                         | DNV-TAA000032X<br>UL MH19482              |
| Degree of protection                                  | IP65<br>With plug socket<br>To IEC 60529  |
| Nominal size  | 11 mm                                     |
| Sealing principle                                     | Soft                                      |
| Mounting position                                     | optional                                  |
| Manual override                                       | Detenting via accessory<br>Non-detenting  |
| Type of piloting                                      | Pilot actuated                            |
| Pilot air supply                                      | Internal                                  |
| Flow direction  | Non-reversible                            |
| Symbol  | 00991656                                  |
| Valve position code                                   | Inscription label holder                  |
| lap   | Overlap                                   |
| Switching time off                                    | 33 ms                                     |
| Switching time on                                     | 50 ms                                     |
| Duty cycle  | 100%                                      |
| Max. positive test pulse with 0 signal                | 3300 µs                                   |
| Max. negative test pulse with 1 signal                | 3100 µs                                   |
| Characteristic coil data                              | 24 V DC: 1.5 W                            |
| Permissible voltage fluctuations                      | -15%/+10%                                 |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4] |

| <b>Feature</b>                     | <b>Value</b>   |
|------------------------------------|--|
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Vibration resistance               | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6           |
| Shock resistance                   | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                          |
| Corrosion resistance class CRC     | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Media temperature                  | -5 °C ... 50 °C  |
| Ambient temperature                | -5 °C ... 50 °C  |
| Electrical connection              | Type C   |
| Type of mounting                   | With through-hole  |
| Pilot exhaust port 82              | M5   |
| Pilot air port 12                  | M5   |
| Pneumatic connection, port 1       | QS-10  |
| Pneumatic connection, port 2       | QS-10  |
| Pneumatic connection, port 3       | G3/8   |
| Note on materials                  | RoHS-compliant   |
| Material seals                     | NBR  |
| Material housing                   | Die-cast aluminium   |