

Ball valve VZBA-1/4"-GGG-63-32L-F0304-V4V4T

Part number: 1692210

FESTO



 General operating condition

Data sheet

| Feature | Value |
|------------------------------|---|
| Design | L-hole |
| Type of actuation | Mechanical |
| Sealing principle | Soft |
| Mounting position | optional |
| Type of mounting | In-line installation |
| Connection Process valve | Rp1/4 |
| Switching position indicator | Slot direction = flow direction |
| Flange hole pattern | F03 F04 |
| Inside diameter | 11.6 mm |
| Nominal size DN | 8 |
| Valve function | 3/2 |
| Manual override | None |
| Flow direction | Reversible |
| Nominal pressure PN | 63 |
| Actuating torque | 13 Nm |
| Based on standard | ISO 5211 |
| Symbol | 00991888 |
| Medium | Compressed air to ISO 8573-1:2010 [-:-:-] Inert gases Water – no water vapour Neutral fluids Other media on request |
| Media temperature | -10 °C ... 200 °C |
| Flow rate Kv L hole | 4.5 m ³ /h |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Material housing | High-alloy stainless steel |
| Material number housing | 1.4408 |
| Material seat seal | PTFE, modified |

| Feature | Value |
|--------------------------------|--|
| Material seals | FPM PTFE PTFE reinforced |
| Material ball | High-alloy stainless steel |
| Material number ball | 1.4408 |
| Material shaft | High-alloy stainless steel |
| Material number shaft | 1.4401 |
| Product weight | 700 g |
| Explosion protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Corrosion resistance class CRC | 3 - high corrosion stress |