

# Trunnion flange ZNCF-50

Part number: 174413

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Size                           | 50                            |
| Based on standard              | ISO 15552                     |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B2-L                |
| Ambient temperature            | -40 °C ... 150 °C             |
| Max. load capacity             | 2.5 kN                        |
| Product weight                 | 473 g                         |
| Note on materials              | RoHS-compliant                |
| Material mounting              | Stainless steel casting       |
| Material screws                | Steel<br>Galvanised           |