

Ball valve VZBA-1/4"-GGG-63-32T-F0304-V4V4T

Part number: 1692220

FESTO



 General operating condition

Data sheet

Feature	Value
Design	T-bore
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Inline installation
Connection Process valve	Rp1/4
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F03 F04
Inside diameter	11.6 mm
Nominal size DN	8
Valve function	3/2
Manual override	None
Flow direction	Reversible
Nominal pressure PN	63
Actuating torque	13 Nm
Based on standard	ISO 5211
Symbol	00991888
Medium	Compressed air to ISO 8573-1:2010 [-:-:-] Inert gases Water – no steam Neutral fluids Other media on request
Media temperature	-10 °C ... 200 °C
Flow rate Kv T hole angled	4.5 m ³ /h
Flow rate Kv T hole straight	8 m ³ /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	High-alloy stainless steel
Material number housing	1,4408

Feature	Value
Material seat seal	PTFE, modified
Material seals	Fluoro rubber PTFE PTFE-reinforced
Material ball	High-alloy stainless steel
Material number ball	1,4408
Material shaft	High-alloy stainless steel
Material number shaft	1,4401
Product weight	700 g
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	3 - high corrosion stress