

Clamping unit KPE-10

Part number: 178465

FESTO



 General operating condition

Data sheet

Feature	Value
Mounting position	optional
Type of clamping with direction of action	on both sides Clamping via spring force, released via compressed air
Design	Tilting wedge mechanism
Variants	Piston rod at one end
Position detection	Without
Safety function	Holding and stopping a movement
Operating pressure	0.3 MPa ... 1 MPa
Operating pressure	3 bar ... 10 bar
Operating pressure	43.5 psi ... 145 psi
Release pressure	≥0.3 MPa
Release pressure	≥3 bar
Round material to be clamped	10 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Static holding force	350 N
Product weight	260 g
Note on materials	RoHS-compliant
Material seals	NBR TPE-U(PU)
Material spring	Spring steel
Material housing	Anodised
Material clamp jaws	Brass
Material piston	POM