

Push-in Y-fitting QSYLV-G3/8-10

Part number: 186211

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal size	5.2 mm
Tubing insertion depth	20.2 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	L-shape, dual, parallel
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.095 MPa ... 0.6 MPa
Operating pressure complete temperature range	-0.95 bar ... 6 bar
Operating pressure complete temperature range	-13.775 psi ... 87 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.4 MPa
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Temperature-dependent operating pressure	-13.775 psi ... 203 psi
Note on operating pressure	Water: max. 0.6 MPa at max. 50°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Note on operating and pilot medium	Lubricated operation possible Water: G-thread only possible with sealing ring type OL as additional accessory
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1
Ambient temperature	-10 °C ... 80 °C
Nominal torque	15.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	73 g
Number of outputs	2
Number of supply lines	1
Type of mounting	Hollow bolt with external hex
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	For tubing outside diameter of 10 mm
Colour of release ring	Blue
Note on materials	RoHS-compliant
Material housing	PBT
Material hollow bolt	Nickel-plated brass

Feature	Value
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel