

# ISO cylinder DSBF-C-50-400-PPVA-N3-R

Part number: 1775268

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 400 mm   |
| Piston diameter  | 50 mm  |
| Piston rod thread  | M16x1.5  |
| Cushioning   | Pneumatic cushioning, adjustable at both ends  |
| Mounting position  | optional   |
| Conforms to standard   | ISO 15552  |
| Piston-rod end   | Male thread  |
| Design   | Piston<br>Piston rod<br>Profile barrel   |
| Position detection   | Via proximity switch   |
| Symbol   | 00991235   |
| Operating pressure   | 0.04 MPa ... 1.2 MPa   |
| Operating pressure   | 0.4 bar ... 12 bar   |
| Mode of operation  | Double-acting  |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 3 - high corrosion stress  |
| LABS (PWIS) conformity                                       | VDMA24364-B2-L   |
| Cleanroom suitability, measured according to ISO 14644-14    | Class 5 according to ISO 14644-1   |
| Ambient temperature  | -20 °C ... 80 °C   |
| Impact energy in end positions                               | 1 J  |
| Cushioning length  | 22 mm  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 990 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1178 N   |
| Moving mass  | 1363 g   |
| Moving mass for 0 mm stroke                                  | 363 g  |
| Additional moving mass per 10 mm stroke                      | 25 g   |
| Product weight   | 3561 g   |
| Basic weight for 0 mm stroke                                 | 1241 g   |
| Additional weight per 10 mm stroke                           | 58 g   |
| Type of mounting   | Via female thread<br>With accessories  |
| Pneumatic connection   | G1/4   |
| Note on materials  | RoHS-compliant   |

| <b>Feature</b>              | <b>Value</b>                     |
|-----------------------------|----------------------------------|
| Material cover              | Coated die-cast aluminium        |
| Material piston seal        | TPE-U(PU)                        |
| Material piston             | Wrought aluminium alloy          |
| Material piston rod         | High-alloy stainless steel       |
| Material piston rod wiper   | TPE-U(PU)                        |
| Buffer seal material        | TPE-U(PU)                        |
| Material of cushioning boss | POM                              |
| Material cylinder barrel    | Anodised wrought aluminium alloy |
| Material nut                | High-alloy stainless steel       |
| Material bearing            | POM                              |
| Material collar screws      | Galvanised steel                 |