


Service unit FRC-1/2-D-5M-O-MIDI

Part number: 192655

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Midi |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical +/-5° |
| Condensate drain | Manual, rotating |
| Design | Proportional standard mist lubricator |
| Max. condensate volume | 43 ml |
| Grade of filtration | 5 µm |
| Bowl guard | Metal bowl guard |
| Symbol | 00991550 |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | Prepared for G1/4 |
| Operating pressure | 0.1 MPa ... 1.6 MPa |
| Operating pressure | 1 bar ... 16 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.02 MPa |
| Max. pressure hysteresis | 0.2 bar |
| Max. pressure hysteresis | 2.9 psi |
| Standard nominal flow rate (standardised to DIN 1343) | 1800 l/min |
| Operating medium | Inert gas |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [6:8:-] Inert gas |
| Media temperature | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1440 g |
| Type of mounting | With accessories |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 2 | G1/2 |
| Note on materials | RoHS compliant |
| Material housing | Die-cast zinc |
| Material bowl | Makrolon® |