


# Vacuum generator VN-10-L-T3-PQ2-VQ2-R01

Part number: 193573

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Nominal size, Laval nozzle	0.95 mm
Grid dimension	14 mm
Silencer design	Open
Mounting position	Any
Ejector characteristic	High suction rate Standard
Integrated function	Open silencer
Design	T-shape
Symbol	00991489
Operating pressure for max. suction flow rate	4 bar
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction flow rate against atmosphere	62.7 l/min
Air supply time at nominal operating pressure	0.46 s
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	0 °C ... 60 °C
Sound pressure level at nominal operating pressure	73 dB(A)
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.5 Nm
Product weight	24 g
Type of mounting	With through-hole With accessories
Pneumatic connection, port 1	QS-6
Pneumatic connection, port 3	Open silencer
Vacuum connection	QS-6
Material connecting thread	Nickel-plated brass
Note on materials	RoHS compliant
Material seals	NBR
Material receiver nozzle	POM
Material housing	Reinforced POM
Material silencer	Packaging unit
Material transmitter nozzle	Wrought aluminium alloy

Feature	Value
Material fitting	Brass nickel-plated