

# Connecting cable KMC-1-230AC-2,5

Part number: 30932

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value   |
|--|---|
| Maritime classification                      | See certificate   |
| Type of mounting                             | On solenoid valve via M3 central screw                                |
| Mounting position                            | optional  |
| Product weight                               | 170 g   |
| Electrical connection                        | Socket<br>Type A  |
| Nominal operating voltage AC                 | 230 V   |
| Reverse polarity protection                  | For all electrical connections  |
| Protective conductor connection              | Available   |
| Cable length                                 | 2.5 m   |
| Cable diameter                               | 6 mm  |
| Cable structure                              | 3 x 0.75 mm <sup>2</sup>  |
| Degree of protection                         | IP67<br>To IEC 60529  |
| Ambient temperature                          | -20 °C ... 80 °C  |
| CE mark (see declaration of conformity)      | To EU Low Voltage Directive<br>In accordance with EU RoHS Directive   |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions<br>To UK regulations for electrical equipment |
| LABS (PWIS) conformity                       | VDMA24364-B2-L  |
| Corrosion resistance class CRC               | 1 - Low corrosion stress  |
| Material cable sheath                        | PVC   |
| Material housing                             | PC  |
| Material electrical contact                  | Bronze  |