

# Semi-rotary drive DSRL-10-180-P-FW

Part number: 33296

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	10
Cushioning angle	2.4 deg
Rotation angle adjustment range	0 deg ... 180 deg
Swivel angle	0 deg ... 180 deg
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Design	Vane
Position detection	Without
Symbol	00991265
Operating pressure	0.25 MPa ... 0.8 MPa
Operating pressure	2.5 bar ... 8 bar
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	3 Hz
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Max. axial force	10 N
Max. radial force	30 N
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	0.5 Nm
Product weight	100 g
Type of mounting	With through-hole
Pneumatic connection	M3
Material covering	PA-reinforced
Material drive shaft	Steel Nickel-plated
Material seals	NBR
Material housing	Die-cast zinc