

Round cylinder DSNU-50-80-PPV-A

Part number: 196043

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	50 mm
Piston rod thread	M16x1.5
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Symbol	00991235
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	1 J
Cushioning length	20 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	989.6 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1178.1 N
Moving mass	613 g
Product weight	1407 g
Type of mounting	With accessories
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy steel
Material cylinder barrel	High-alloy stainless steel